

## Label sheet, DIN A4 - BMKL 18X 6,5 OG - 5036147

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Label sheet, DIN A4, Sheet, orange, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, Office printing systems, mounting type: adhesive, lettering field size: 18 x 6.5 mm, Number of individual labels: 360



### Your advantages

- The unperforated SK U ... sheets are available for custom label designs
- These labels have been specially developed for laser printers
- Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- The material file can be downloaded under the CLIP PROJECT software under Downloads - "Software update - Marking".
- Can be printed on all commercially available laser printers

### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 095864
GTIN	4017918095864
Weight per Piece (excluding packing)	15.010 g
Custom tariff number	39199080
Country of origin	Belgium
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	6.5 mm
Width (a)	18 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
---------------------------------	------------------

#### General

Note	Print image may vary depending on laser printer
------	---

# Label sheet, DIN A4 - BMKL 18X 6,5 OG - 5036147

## Technical data

### General

Color	orange
Base element material	Polyester
Components	Silicone-free
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	360
Number of individual labels per row	9
Marking mounting type	adhesive

### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Classifications

### eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504

# Label sheet, DIN A4 - BMKL 18X 6,5 OG - 5036147

## Classifications

### UNSPSC

UNSPSC 21.0	39131504
-------------	----------

## Accessories

### Accessories

#### Printing system accessories

Accessories - CMS-P1-PAD - 5144819



Accessories