

Warning label - WS UT 10 - 3047361

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Warning sign for UT terminal blocks



Your advantages

- ✓ Can be isolated lengthwise and crosswise
- ✓ Accidental actuation of the terminal points is prevented
- ✓ Warning labels and warning covers serve to cover and identify mains terminal blocks
- ✓ The warning labels snap into the screw and actuation shafts of the relevant terminal block

RoHS

Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 073950
GTIN	4046356073950
Weight per Piece (excluding packing)	1.900 g
Custom tariff number	49119900
Country of origin	Poland

Technical data

Dimensions

Length (b)	25.2 mm
Width (a)	10.2 mm
Height (c)	25.2 mm
Diameter	0.00 mm

Ambient conditions

Ambient temperature (operation)	-60 °C ... 130 °C
---------------------------------	-------------------

General

Warning label - WS UT 10 - 3047361

Technical data

General

Color	yellow/black
Type	Rectangle
Components	free from silicone and halogen
Flammability rating according to UL 94	V0
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	Lightning flash
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	screw, rivet

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 10.0.1	40200202
eCl@ss 4.0	40200100
eCl@ss 4.1	40200100
eCl@ss 5.0	40200100
eCl@ss 5.1	27141100
eCl@ss 6.0	40200100
eCl@ss 7.0	40200103
eCl@ss 8.0	40200202
eCl@ss 9.0	40200202

ETIM

ETIM 2.0	EC000761
----------	----------

Warning label - WS UT 10 - 3047361

Classifications

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001777
ETIM 6.0	EC001777
ETIM 7.0	EC001777

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	55121718
UNSPSC 18.0	55121718
UNSPSC 19.0	55121718
UNSPSC 20.0	55121718
UNSPSC 21.0	55121718