

Replacement die - CRIMPFOX-M RCI 6/DIE - 1212073

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Die, for Crimpfox-M, for insulated cable lugs 0.1 - 0.4 mm² and 4 - 6 mm² (light green, yellow), packed in a serial storage box

Key Commercial Data

| | |
|--------------------------------------|---------------|
| Packing unit | 1 pc |
| GTIN | |
| GTIN | 4046356452526 |
| Weight per Piece (excluding packing) | 80.400 g |
| Custom tariff number | 82032000 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|------------|---------|
| Length (b) | 114 mm |
| Width (a) | 75 mm |
| Height (c) | 25.5 mm |

General

| | |
|--------------------|----------------------|
| Color | black |
| Compression | Oval crimp |
| Type of contact | Insulated cable lugs |
| Designation | Crimping position 1 |
| Min. cross section | 0.1 mm ² |
| Max. cross section | 0.4 mm ² |
| AWG min | 26 |
| AWG max | 22 |
| Designation | Crimping position 2 |
| Min. cross section | 4 mm ² |
| Max. cross section | 6 mm ² |
| AWG min | 12 |
| AWG max | 10 |
| Weight | 66 g |

Replacement die - CRIMPFOX-M RCI 6/DIE - 1212073

Technical data

General

| | |
|--------------------|---------------------|
| Min. cross section | 0.1 mm ² |
| Max. cross section | 6 mm ² |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 21019290 |
| eCl@ss 4.0 | 21040300 |
| eCl@ss 4.1 | 21040300 |
| eCl@ss 5.0 | 21040300 |
| eCl@ss 5.1 | 21040300 |
| eCl@ss 6.0 | 21043800 |
| eCl@ss 7.0 | 21043811 |
| eCl@ss 8.0 | 21043811 |
| eCl@ss 9.0 | 21019290 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001186 |
| ETIM 3.0 | EC001186 |
| ETIM 4.0 | EC001282 |
| ETIM 5.0 | EC001282 |
| ETIM 6.0 | EC001282 |
| ETIM 7.0 | EC001282 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 27112118 |
| UNSPSC 7.0901 | 27111518 |
| UNSPSC 11 | 23171604 |
| UNSPSC 12.01 | 27111518 |
| UNSPSC 13.2 | 27111518 |
| UNSPSC 19.0 | 27111518 |

Approvals

Approvals

Approvals


EAC

Ex Approvals

Replacement die - CRIMPFOX-M RCI 6/DIE - 1212073

Approvals

Approval details

| | | |
|-----|---|--------------------------|
| EAC |  | RU x- DE.xx08.B.02974 |
|-----|---|--------------------------|

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>