

Cable marker carrier - GKM 1 GY - 1750498

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable marker carrier, gray, unlabeled, mounting type: clip on, cable diameter range: 0 ... 5.2 mm, lettering field size: 20 mm x 8 mm

Your advantages

- SS-ZB ..., UC-TM ... or ZB ... can be used for labeling purposes
- The conductor marker is attached directly to a conductor

Key Commercial Data

Packing unit	100 pc
GTIN	
GTIN	4017918028299
Weight per Piece (excluding packing)	2.200 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	20 mm
Width (a)	9 mm
Cable diameter	0 mm ... 5.2 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

General

Color	gray
Type	Mounting set
Components	free from silicone and halogen
Flammability rating according to UL 94	V2

Cable marker carrier - GKM 1 GY - 1750498

Technical data

General

Material	PA/ABS
Marking mounting type	clip on

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Classifications

eCl@ss

eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27149100
eCl@ss 7.0	27149153
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC002248
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Device marking

Cable marker carrier - GKM 1 GY - 1750498

Accessories

Contactor marker - zack marker strip - SS-ZB WH - 5031171



Contactor marker - zack marker strip, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, mounting type: snap into flat marker groove, lettering field size: 20 mm x 8 mm, Number of individual labels: 5

Contactor marker - zack marker strip - SS-ZB YE - 5031650



Contactor marker - zack marker strip, Strip, yellow, unlabeled, can be labeled with: CMS-P1-PLOTTER, mounting type: snap into flat marker groove, lettering field size: 20 mm x 8 mm, Number of individual labels: 5

Snap-in markers - UC-EM (20X9) - 0825503



Snap-in markers, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 20 x 9 mm, Number of individual labels: 20

Snap-in markers - UC-EM (20X9) YE - 0827637



Snap-in markers, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID COLOR, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 20 x 9 mm, Number of individual labels: 20

Snap-in markers - UCT-EM (20X9) - 0801471



Snap-in markers, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 20 x 9 mm, Number of individual labels: 24

Cable marker carrier - GKM 1 GY - 1750498

Accessories

Snap-in markers - UCT-EM (20X9) YE - 0801472



Snap-in markers, Sheet, yellow, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 20 x 9 mm, Number of individual labels: 24

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>