

Fabric label - MM-EMLC (EX12)R C1 WH/BK - 0803934

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Highly flexible textile label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4055626212142
Weight per Piece (excluding packing)	51.600 g
Custom tariff number	96121010
Country of origin	China

Technical data

Dimensions

Length (b)	6000 mm
Width (a)	12 mm

Ambient conditions

Ambient temperature (operation)	0 °C ... 80 °C
Recommended storage conditions	5 - 35°C / 30 - 80 % relative humidity. Storage in a cool and dry place in the original packaging is recommended.

General

Color	white
Components	free from silicone, halogen, and cadmium
Material	PA
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed

Fabric label - MM-EMLC (EX12)R C1 WH/BK - 0803934

Technical data

General

Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	adhesive

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410

Fabric label - MM-EMLC (EX12)R C1 WH/BK - 0803934

Classifications

UNSPSC

UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504