

Tool set - SF-SL/PZ SET - 1212542

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screwdriver set, bladed/crosshead Pozidriv[®], 6-part, incl. rack

Your advantages

- The SF-SL ... screwdriver sets are available with a variety of contents
- Wall-mountable screwdriver rack included

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 589772
GTIN	4046356589772
Weight per Piece (excluding packing)	636.000 g
Custom tariff number	82054000
Country of origin	Czech Republic

Technical data

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Articles in set

Screwdriver - SF-SL 0,5X3,0-80 - 1212548



Screwdriver, slot-headed, size: 0.5 x 3.0 x 80 mm, 2-component grip, with non-slip grip

Tool set - SF-SL/PZ SET - 1212542

Articles in set

Screwdriver - SF-SL 0,8X4,0-100 - 1212551



Screwdriver, bladed (lasered), size: 0.8 x 4.0 x 100 mm, 2-component grip, with non-slip grip

Screwdriver - SF-SL 1,0X5,5-150 - 1212552



Screwdriver, bladed (lasered), size: 1.0 x 5.5 x 150 mm, 2-component grip, with non-slip grip

Screwdriver - SF-SL 1,2X6,5-150 - 1212553



Screwdriver, bladed (lasered), size: 1.2 x 6.5 x 150 mm, 2-component grip, with non-slip grip

Philips screwdriver - SF-PZ 1-80 - 1212563



Screwdriver, PZ crosshead (lasered), uninsulated, size: PZ 1 x 80, 2-component grip, with non-slip grip

Philips screwdriver - SF-PZ 2-100 - 1212564



Screwdriver, PZ crosshead (lasered), uninsulated, size: PZ 2 x 150, 2-component grip, with non-slip grip

Classifications

eCl@ss

eCl@ss 10.0.1	21045003
eCl@ss 4.0	21040200

Tool set - SF-SL/PZ SET - 1212542

Classifications

eCl@ss

eCl@ss 4.1	21040200
eCl@ss 5.0	21040200
eCl@ss 5.1	21040200
eCl@ss 6.0	21040200
eCl@ss 7.0	21045003
eCl@ss 8.0	21045003
eCl@ss 9.0	21045003

ETIM

ETIM 4.0	EC000149
ETIM 5.0	EC000149
ETIM 6.0	EC000149
ETIM 7.0	EC000149

UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27113201
UNSPSC 18.0	27113201
UNSPSC 19.0	27113201
UNSPSC 20.0	27113201
UNSPSC 21.0	27113201

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01750
-----	---	--------------------------

