


## Screw plug - A-INSP-M20-65N-P-BK - 1415206

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Screw plug, material: PA, connecting thread: M20 x 1.5, color: jet black RAL 9005, with O-ring



### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 055626 038513
GTIN	4055626038513
Weight per Piece (excluding packing)	4.970 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### Dimensions

Length	9.5 mm
Connecting thread diameter	20 mm
Hexagon angular dimension	24 mm (Diameter)
Length of the connecting thread	6 mm

#### Ambient conditions

Degree of protection (IP)	IP68
	IP66
Ambient temperature (operation)	-40 °C ... 100 °C

#### General

Material	PA
Sealing material	EPDM (O-ring)
Thread type on connection side	M20 x 1.5
Torque	1 Nm

# Screw plug - A-INSP-M20-65N-P-BK - 1415206

## Technical data

### General

Color	jet black RAL 9005
Manufacturer	WISKA
Manufacturer Designation	EVSG-ORD 20

### Standards and Regulations


Halogen-free	yes
--------------	-----

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings

Dimensional drawing



## Classifications

### eCl@ss

eCl@ss 10.0.1	23111190
eCl@ss 4.0	23111100
eCl@ss 4.1	23111100
eCl@ss 5.0	23111100

## Screw plug - A-INSP-M20-65N-P-BK - 1415206

### Classifications

#### eCl@ss

eCl@ss 5.1	23111100
eCl@ss 6.0	23111100
eCl@ss 7.0	23111190
eCl@ss 8.0	23111190
eCl@ss 9.0	23111190

#### ETIM

ETIM 4.0	EC000032
ETIM 5.0	EC000032
ETIM 6.0	EC000032
ETIM 7.0	EC000032

#### UNSPSC

UNSPSC 13.2	31161501
UNSPSC 18.0	31261502
UNSPSC 19.0	31261502
UNSPSC 20.0	31261502
UNSPSC 21.0	31261502

### Accessories

#### Accessories

##### Flat nut

Counter nut - A-INL-M20-P-BK - 1411215



Counter nut, material: PA, for threads M20 x 1.5, color: jet black RAL 9005