


Part number:

451058

PCB Image

- Material FR2
- PCB Thickness 1.6mm
- Layer Count 1 layer
- Copper weight 1oz(35um)
- Surface finish OSP
- Circuit Size 160.00mm x 100.00mm
- Hole count 2235
- Smallest hole 1.00mm
- Number of test points 2235



GSPK CIRCUITS, MARKET LEADING, GLOBAL SUPPLIER OF

PCB's FROM SINGLE SIDED TO 24 LAYER

QUALITY



ABOUT US



GSPK Circuits Ltd. is a market leading, global supplier of Printed Circuit Boards. We focus on Fast-turn PCB's, Prototyping and Specialist PCB's. Our team manages your PCB's and ensures you get a product with the highest quality. Having the 'Lean Champion' status, you're ensured a fast and agile approach to PCB manufacture in one of our world class manufacturing divisions.

CONTACT


GSPK Circuits Ltd
Wetherby Road, Boroughbridge
North Yorkshire
YO51 9UY
United Kingdom
☎ +44(0) 1423 798 740
✉ enquiries@gspkcircuits.ltd.uk

Teilenummer:

451058

Echte Produktansicht


- | | |
|-------------------------|---------------------|
| • Material | FR2 |
| • PCB Dicke | 1.6mm |
| • layer-anzahl | einseitig |
| • Kupfergewicht | 1 oz(35um) |
| • Oberflächenveredlung | OSP |
| • Schaltkreisgröße | 160.00mm x 100.00mm |
| • Anzahl der Löcher | 2235 |
| • kleinstes Loch | 1.00mm |
| • Anzahl der Prüfpunkte | 2235 |



GSPK CIRCUITS, MARKET LEADING, GLOBAL SUPPLIER OF

PCB's FROM SINGLE SIDED TO 24 LAYER

QUALITY



ABOUT US



GSPK Circuits Ltd. is a market leading, global supplier of Printed Circuit Boards. We focus on Fast-turn PCB's, Prototyping and Specialist PCB's. Our team manages your PCB's and ensures you get a product with the highest quality. Having the 'Lean Champion' status, you're ensured a fast and agile approach to PCB manufacture in one of our world class manufacturing divisions.

CONTACT


GSPK Circuits Ltd
Wetherby Road, Boroughbridge
North Yorkshire
YO51 9UY
United Kingdom
☎ +44(0) 1423 798 740
✉ enquiries@gspkcircuits.ltd.uk

Numéro de pièce:

451058

Image du PCB

- Matériel FR4
- Épaisseur du PCB 1.6mm
- Nombre de couches 1 couche
- Poids de cuivre 1 oz(35um)
- Finition de surface OSP
- Taille du circuit 160.00mm x 100.00mm
- Nombre de trous 2235
- Le plus petit trou 1.00mm
- Nombre de points de test 2235



GSPK CIRCUITS, MARKET LEADING, GLOBAL SUPPLIER OF

PCB's FROM SINGLE SIDED TO 24 LAYER



CONTACT

GSPK Circuits Ltd
Wetherby Road, Boroughbridge
North Yorkshire
YO51 9UY
United Kingdom
☎ +44(0) 1423 798 740
✉ enquiries@gspkcircuits.ltd.uk

QUALITY



ABOUT US




GSPK Circuits Ltd. is a market leading, global supplier of Printed Circuit Boards. We focus on Fast-turn PCB's, Prototyping and Specialist PCB's. Our team manages your PCB's and ensures you get a product with the highest quality. Having the 'Lean Champion' status, you're ensured a fast and agile approach to PCB manufacture in one of our world class manufacturing divisions.

Número de pieza:

451058

Número de pieza:

- Material FR4
- PCB Grosor 1.6mm
- Recuento de capas 1 capa
- Peso de cobre 1 oz(35um)
- Acabado de superficie OSP
- Tamaño del circuito 160.00mm x 100.00mm
- Recuento de agujeros 2235
- Agujero más pequeño 1.00mm
- Numero de puntos de prueba 2235



GSPK CIRCUITS, MARKET LEADING, GLOBAL SUPPLIER OF

PCB's FROM SINGLE SIDED TO 24 LAYER



CONTACT

GSPK Circuits Ltd
Wetherby Road, Boroughbridge
North Yorkshire
YO51 9UY
United Kingdom
☎ +44(0) 1423 798 740
✉ enquiries@gspkcircuits.ltd.uk

QUALITY



ABOUT US



GSPK Circuits Ltd. is a market leading, global supplier of Printed Circuit Boards. We focus on Fast-turn PCB's, Prototyping and Specialist PCB's. Our team manages your PCB's and ensures you get a product with the highest quality. Having the 'Lean Champion' status, you're ensured a fast and agile approach to PCB manufacture in one of our world class manufacturing divisions.