


PRODUCT-DETAILS

# PS1-3-1-65

## PS1-3-1-65 Busbar



### General Information

Extended Product Type	PS1-3-1-65
Product ID	1SAM201906R1113
EAN	4013614400735
Catalog Description	PS1-3-1-65 Busbar
Long Description	PS1-3-1-65 3-phase busbar for 3 MS116 / MS132 with 1 HK/SK, Ie=65A

### Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85369010

### Popular Downloads

Data Sheet, Technical Information	1SBC100192C02--
Instructions and Manuals	2CDC131011M6802 2CDC131034M6801 2CDC131022M6802
Dimension Diagram	1SAM200450F0006

### Dimensions

Product Net Width	149.5 mm
-------------------	----------

Product Net Height	32.3 mm
Product Net Depth / Length	13 mm
Product Net Weight	0.06 kg

## Technical

Rated Operational Voltage	690 V AC 250 V DC
Rated Operational Current (I <sub>e</sub> )	65 A
Rated Impulse Withstand Voltage (U <sub>imp</sub> )	6 kV
Rated Short-time Withstand Current (I <sub>cw</sub> )	100 kA
Number of Mountable Devices	3
Number of Lateral Auxiliary Contacts	1
Number of Phases	3
Number of Poles	9
Degree of Protection	IP20
Pollution Degree	3
Connection Type	Fork
Standards	IEC/EN 60947-1 IEC/EN 60947-4-1 UL 60947-1 UL 60947-4-1
Product Name	Busbar
Suitable For	MS116 MS132
Suitable for Product Class	Manual Motor Starter
Accessory Group	Electrical
Accessory Type	3-Phase Busbar

## Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V AC
Ampere Rating UL/CSA	65 A

## Environmental

Ambient Air Temperature	Operation -25 ... +70 °C Storage -50 ... +80 °C
RoHS Status	Following EU Directive 2011/65/EU

## Certificates and Declarations (Document Number)

cUL Certificate	1SAA963001-1701
Declaration of Conformity - CE	1SAD938513-0056
GOST Certificate	1SAA937000-2703
Instructions and Manuals	2CDC131011M6802 2CDC131034M6801 2CDC131022M6802
RoHS Information	1SAD938511-0056

UL Certificate

1SAA963001-1602

### Container Information

Package Level 1 Width	80 mm
Package Level 1 Depth / Length	181 mm
Package Level 1 Height	46 mm
Package Level 1 Gross Weight	0.638 kg
Package Level 1 EAN	4013614488115
Package Level 1 Units	box 10 piece

### Classifications

Object Classification Code	W
ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 5	EC000215 - Phase busbar
ETIM 6	EC000215 - Phase busbar
ETIM 7	EC000215 - Phase busbar
eClass	7.0 27371306
UNSPSC	39121117
IDEA Granular Category Code (IGCC)	4378 >> Phase busbar
E-Number (Sweden)	3111680

### Categories

Low Voltage Products and Systems → Control Products → Manual Motor Starters → Manual Motor Starters Accessories

