

USB 3.0 to HDMI VGA Adapter - 4K 30Hz

Product ID: USB32HDVGA



This USB 3.0 to HDMI VGA adapter offers a portable solution for connecting an HDMI and VGA display to your USB-A laptop or desktop computer. The multiport video adapter lets you mirror or extend content on two additional monitors simultaneously (1 x HDMI and 1 x VGA), creating a dual-screen workstation.

Enhance Your Productivity

Functioning as an external graphics card, this multi-display adapter provides a convenient way to add multi-monitor capability to a USB 3.0 desktop or laptop computer.

Leveraging the USB 3.0 interface, the adapter delivers high-definition content to your HDMI and VGA displays. The adapter can be used to mirror your primary desktop, or to extend your desktop to double your workspace and increase your productivity.

Two-in-One Video Connectivity with Travel in Mind

Avoid the hassle of carrying different adapters. This USB 3.0 video converter provides both HDMI and VGA outputs, you can conveniently connect your laptop to any HDMI and VGA-equipped display or projector, using this multiport adapter.

The lightweight dongle also features a small footprint, making it the perfect accessory for professionals on-the-go.

Astonishing 4K Picture Quality

The HDMI output on this USB 3.0 video adapter supports UHD resolutions up to 4K 30Hz, while the VGA output supports HD resolutions up to 1920 x 1080, ensuring you won't have to sacrifice picture quality.

USB32HDVGA is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect to virtually any HDMI and VGA display while traveling or in the office
- Add multi-monitor capabilities to a single USB 3.0 computer
- Run multiple applications on dual screens simultaneously

Features

- Maximize your laptop's video compatibility with a 2-in-1 adapter: USB-A to HDMI® and VGA
- Support resource-demanding applications with UHD resolutions up to 4K 30Hz
- Boost your productivity by creating a dual screen workstation in the office or while traveling

Hardware	Warranty	3 Years
	Active or Passive Adapter	Active
		Passive
	Audio	Yes
	AV Input	USB 3.0
	AV Output	HDMI
		VGA
Chipset ID	Silicon Motion - SM768	
Industry Standards	USB 3.0 Compliant	
Performance	Audio Specifications	HDMI - 7.1 Channel Audio
		VGA - No Audio Support
	General Specifications	This USB video adapter uses a Silicon Motion family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a DisplayLink, MCT or Fresco family chipset.
	Supported Resolutions	HDMI: 3840x2160 (4K) 30Hz VGA: 1920x1080 60Hz
		<i>Lower resolutions and refresh rates may also be supported</i>
	Video Revision	HDMI 1.4
Wide Screen Supported	Yes	
Connector(s)	Connector A	1 - USB Type-A (9 pin) USB 3.0 Male Input
	Connector B	1 - VGA (14 pin, High Density D-Sub) Female Output
		1 - HDMI Female Output
Environmental	Humidity	0~95% RH Non-condensing
	Operating Temperature	-10°C to 55°C (14°F to 131°F)
	Storage Temperature	-25°C to 75°C (32°F to 167°F)
Physical Characteristics	Cable Length	4.3 in [109.2 mm]
	Color	Black & Silver
	Material	Plastic
	Product Height	14.000
	Product Length	10.6 in [27 cm]
	Product Width	43.000

	Weight of Product	54.000
Packaging Information	Package Height	30.000
	Package Length	170.000
	Package Width	145.000
	Shipping (Package) Weight	112.000
What's in the Box	Included in Package	1 - USB-A to HDMI and VGA Adapter

Product appearance and specifications are subject to change without notice.