

PRODUCT-DETAILS

CR-S024VADC1CRS

CR-S024VADC1CRS Interface relay cpl. 1c/o, A1-A2=24VAC/DC, Output=6A/250VAC



General Information

Extended Product Type	CR-S024VADC1CRS
Product ID	1SVR405541R3110
EAN	4013614499289
Catalog Description	CR-S024VADC1CRS Interface relay cpl. 1c/o, A1-A2=24VAC/DC, Output=6A/250VAC
Long Description	CR-S024VADC1CRS Interface relay cpl. 1c/o, A1-A2=24VAC/DC, Output=6A/250VAC screw terminals

Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	85364900

Popular Downloads

Data Sheet, Technical Information	2CDC117022D0201
Instructions and Manuals	2CDC117022D0201

Dimensions

Product Net Width	6.3 mm
Product Net Height	76.4 mm

Product Net Depth / Length	88.5 mm
Product Net Weight	0.03 kg

Technical

Function	Fully assembled interface relay CR-S
Sub-Function	Relay with standard contacts
Output	1 c/o (SPDT) contact
Output Signal	250 V / 6 A
Rated Control Supply Voltage (U _s)	24 V AC/DC
Terminal Type	Screw Terminals

Environmental

Ambient Air Temperature	Operation -40 ... +70 °C Storage 0 ... +40 °C
RoHS Status	Following EU Directive 2011/65/EU

Technical UL/CSA

Connecting Capacity UL/CSA	Flexible 14 AWG Rigid 14 AWG
Tightening Torque UL/CSA	4.42 in-lb

Certificates and Declarations (Document Number)

CSA Certificate	CSA_262671-2785865
cURus Certificate	cURus508_E244328
Declaration of Conformity - CE	1SVD982017-0001
EAC Certificate	EAC_RU_C-PL.ME77.B.01873
Environmental Information	1SAA981009-2403
Instructions and Manuals	2CDC117022D0201
RoHS Information	1SVD982017-0001

Container Information

Package Level 1 Units	10 piece
Package Level 1 Width	93 mm
Package Level 1 Height	81 mm
Package Level 1 Depth / Length	66 mm
Package Level 1 Gross Weight	0.32 kg
Package Level 1 EAN	4013614486654

Classifications

Object Classification Code	K
ETIM 4	EC001437 - Switching relay
ETIM 5	EC001437 - Switching relay

ETIM 6	EC001437 - Switching relay
ETIM 7	EC001437 - Switching relay
eClass	7.0 27371601
E-Number (Sweden)	4001400

Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Interface Relays and Optocouplers

