

## Plug-in board - IBS UNI DIO - 2753672


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Universal I/O module in the form of a daughterboard



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 153526
GTIN	4017918153526
Weight per Piece (excluding packing)	20.000 g
Custom tariff number	85389091
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Width	70 mm
Height	10 mm
Length	50 mm

#### Ambient conditions

Ambient temperature (operation)	0 °C ... 70 °C
---------------------------------	----------------

#### Module

IC power supply voltage	5 V DC ±10 % (DC)
Typical current consumption	120 mA (90 mA kernel)
Connection method	Remote bus
Interface	INTERBUS
Internal data length	10 bytes IN and 10 bytes OUT data

# Plug-in board - IBS UNI DIO - 2753672

## Technical data

### Module

User interface	60-pos. female connector for power supply, -Diagnostics, -Configuration, -Parallel port for 32 data bits (configurable), -Parallel port for micro-processor
Protocol chip	INTERBUS SUP1 3

### General

Type	Daughterboard
------	---------------

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 4.0	27250200
eCl@ss 4.1	27250200
eCl@ss 5.0	27249200
eCl@ss 5.1	27249200
eCl@ss 6.0	27242600
eCl@ss 7.0	27242605
eCl@ss 8.0	27242608
eCl@ss 9.0	27242605

### ETIM

ETIM 2.0	EC001433
ETIM 3.0	EC001601
ETIM 4.0	EC001601
ETIM 5.0	EC001604
ETIM 6.0	EC001601
ETIM 7.0	EC001601

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	39121724
UNSPSC 18.0	32151602
UNSPSC 19.0	32151602
UNSPSC 20.0	32151602

# Plug-in board - IBS UNI DIO - 2753672

## Classifications

### UNSPSC

UNSPSC 21.0	32151602
-------------	----------

## Approvals

### Approvals

---

### Approvals


EAC

---

### Ex Approvals

---

## Approval details

EAC		EAC-Zulassung
-----	--	---------------

---