

## Adapter cable - CABLE- 9/8/250/RSM/ELAU - 2902984

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Cable adapter for PSR over-speed safety relays (PSR-RSM4 and PSR-MM30), 9/8-pos., cable length: 2.5 m, for controller: ELAU



The figure shows a comparable item from Phoenix Contact



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 701938
GTIN	4046356701938
Weight per Piece (excluding packing)	155.900 g
Custom tariff number	85444290
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Fixed cable length	2.5 m
--------------------	-------

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C (for fixed installation)
	0 °C ... 50 °C (for flexible installation)
Ambient temperature (storage/transport)	-20 °C ... 70 °C

#### General

Connection 1	To the device
Connection method	RJ45
Number of positions	8
Connection 2	Encoder / PLC
Connection method	D-SUB 9 plug/D-SUB 9 socket

# Adapter cable - CABLE- 9/8/250/RSM/ELAU - 2902984

## Technical data

### General

Number of positions	9
Cable resistance	≤ 260 Ω/km
Outer sheath, material	LSHF (FRNC)
Conductor material	Bare Cu litz wires
Shielding	Plastic-coated aluminum foil, tinned copper braided shield
	Soldering on D-SUB housing
Conductor cross section	0.48 mm <sup>2</sup> (AWG 26)

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 10.0.1	27149290
eCl@ss 4.0	27371100
eCl@ss 4.1	27371100
eCl@ss 5.0	27149200
eCl@ss 5.1	27149200
eCl@ss 6.0	27149200
eCl@ss 7.0	27149290
eCl@ss 8.0	27149290
eCl@ss 9.0	27149290

### ETIM

ETIM 2.0	EC001449
ETIM 3.0	EC001449
ETIM 4.0	EC002608
ETIM 5.0	EC002783
ETIM 6.0	EC002783
ETIM 7.0	EC002783

### UNSPSC

UNSPSC 6.01	30211901
UNSPSC 7.0901	39121501
UNSPSC 11	39121501
UNSPSC 12.01	39121501
UNSPSC 13.2	26121641
UNSPSC 18.0	26121641
UNSPSC 19.0	26121641

# Adapter cable - CABLE- 9/8/250/RSM/ELAU - 2902984

## Classifications

### UNSPSC

UNSPSC 20.0	26121641
UNSPSC 21.0	26121641

## Approvals

### Approvals

---

### Approvals

### EAC

---

### Ex Approvals

---

## Approval details

EAC		RU* DE.HB*35.B00385
-----	---	------------------------

---