

Door position switch - PLD E 400-DS-3,0/FS/0,6 - 2702336

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Door position switch with 3 m cable with open cable end and 0.6 m cable with M8 socket (Snap-in), including mounting accessories

Product Description

This door position switch is used to automatically switch the class 400 PLD enclosure lights on or off when opening or closing the control cabinet door. If the enclosure lights are connected in series, this door position switch is to be used before the first light.

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 127453
GTIN	4055626127453
Weight per Piece (excluding packing)	174.000 g
Custom tariff number	85365080
Country of origin	Germany

Technical data

Dimensions

Width	31 mm
Height	30.5 mm
Depth	98.3 mm
Note on dimensions	Without connected cables

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Degree of protection	IP54

General

Color	black
Net weight	174 g
Mechanical service life	10x 10 ⁶ cycles

Door position switch - PLD E 400-DS-3,0/FS/0,6 - 2702336

Technical data

General

Mounting position	any
-------------------	-----

Power supply for module electronics

Rated voltage	24 V DC
Rated current	3 A

Standards and Regulations

Protection class	II
------------------	----


Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Door position switch - PLD E 400-DS-3,0/FS/0,6 - 2702336

Circuit diagram



Classifications

eCl@ss

eCl@ss 4.0	27142500
eCl@ss 4.1	27142500
eCl@ss 5.0	27142500
eCl@ss 5.1	27142500
eCl@ss 7.0	27119220
eCl@ss 8.0	27119220
eCl@ss 9.0	27119290

ETIM

ETIM 5.0	EC002557
----------	----------

Door position switch - PLD E 400-DS-3,0/FS/0,6 - 2702336

Classifications

ETIM

ETIM 6.0	EC002557
ETIM 7.0	EC002557

UNSPSC

UNSPSC 13.2	39111541
UNSPSC 18.0	39111541
UNSPSC 19.0	39111541
UNSPSC 20.0	39111541
UNSPSC 21.0	39111541

Approvals

Approvals

Approvals

UL Listed / cUL Listed / cULus Listed

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
-----------	--	---	---------------

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
------------	--	---	---------------

cULus Listed			
--------------	--	--	--

Accessories

Accessories

Sensor/actuator cable

Door position switch - PLD E 400-DS-3,0/FS/0,6 - 2702336

Accessories

Sensor/actuator cable - SAC-3P-M 8MS/ 0,6-PUR/M 8SIFS - 1417699



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug straight M8, on Socket straight M8 Snap-in, cable length: 0.6 m

Sensor/actuator cable - SAC-3P-M 8MS/ 1,0-PUR/M 8SIFS - 1417700



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug straight M8, on Socket straight M8 Snap-in, cable length: 1 m

Sensor/actuator cable - SAC-3P-M 8MS/ 3,0-PUR/M 8SIFS - 1417701



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug straight M8, on Socket straight M8 Snap-in, cable length: 3 m
