

Tool set - SF-SOCKET SET 47 - 1200292

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



1/4" socket set, 47-piece, 1/4" reversible ratchet, 48 teeth with fast locking system, 50 mm and 100 mm 1/4" extensions, 1/4" screwdriver handle, 150 mm 1/4" flexible extension, 1/4" Cardan joint, 1/4" T-handle
 2 x 1/4" bit adapter, 13 knurled 1/4" sockets, wrench size: 4 / 4.5 / 5 / 5.5 / 6 / 7 / 8 / 9 / 10 / 11 / 12 / 13 / 14 mm, 21 knurled socket bits: 6 x Torx® T10, T15, T20, T25, T30, T40, 6 x Hex 3, 4, 5, 6, 7, 8 mm, 3 x Phillips recess® PH1, PH2, PH3, 3 x Pozidriv® PZ1, PZ2, PZ3, 3 x slotted 4, 5.5, 7 mm, Allen wrench Hex 1.27, 1.5, 2, 2.5 mm, breakage and impact-resistant plastic case with metal fastening

Your advantages

- ✓ Solid 1/4" screw set with comprehensive equipment
- ✓ Ratcheting mechanism with 48 teeth enables precise working, even in tight working environments
- ✓ Optimum power transmission without damaging the screw head, thanks to special edge geometries
- ✓ Robust cases for safe storage
- ✓ Made from chrome vanadium steel for a long service life

Key Commercial Data

| | |
|--------------------------------------|---------------|
| Packing unit | 1 pc |
| GTIN | |
| GTIN | 4055626388113 |
| Weight per Piece (excluding packing) | 1,603.400 g |
| Custom tariff number | 82060000 |
| Country of origin | Taiwan |

Technical data

Environmental Product Compliance

| | |
|---------------------------|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |
|---------------------------|---|

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 21045003 |
| eCl@ss 7.0 | 21045003 |
| eCl@ss 9.0 | 21045003 |

ETIM

| | |
|----------|----------|
| ETIM 6.0 | EC000149 |
|----------|----------|

Tool set - SF-SOCKET SET 47 - 1200292

Classifications

ETIM

| | |
|----------|----------|
| ETIM 7.0 | EC000149 |
|----------|----------|

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

| | | |
|-----|--|--------------------------|
| EAC |  | RU C- DE.AI30.B.01750 |
|-----|--|--------------------------|
