


Cutting tool - PPS STANDARD M - 1206175

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Profile cutter, for cutting and stamping holes in standard DIN rails, NS 32/NS 35/7,5/NS 35/15 and for cutting the NS 15 and NLS-CU 3/10 neutral busbar to length, can accommodate 2 stamping bits, with metric measuring rail, delivered without stamping bits

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 163280
GTIN	4017918163280
Weight per Piece (excluding packing)	18,925.000 g
Custom tariff number	82034000
Country of origin	Germany

Technical data

Dimensions

Length (b)	100 mm
Width (a)	180 mm
Height (c)	220 mm
Length of the measuring bar	1000 mm
Max. material thickness	3 mm

General

Color	black
Type	Millimeter
Weight	19 kg

Classifications

eCl@ss

eCl@ss 10.0.1	21043714
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21049100

Cutting tool - PPS STANDARD M - 1206175

Classifications

eCl@ss

eCl@ss 6.0	21049100
eCl@ss 7.0	21043714
eCl@ss 8.0	21043714
eCl@ss 9.0	21043714

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC000385
ETIM 5.0	EC002212
ETIM 6.0	EC002212
ETIM 7.0	EC002212

UNSPSC

UNSPSC 6.01	23171604
UNSPSC 7.0901	23171604
UNSPSC 11	23171604
UNSPSC 12.01	23171604
UNSPSC 13.2	27111507
UNSPSC 18.0	27111507
UNSPSC 19.0	27111507
UNSPSC 20.0	27111507
UNSPSC 21.0	27111507

Accessories

Accessories

Conversion kit

Stamping bit - PPS-ST (3,5X12)L - 1203563



Stamping bit, for elongated holes: 3.5 x 12 mm

Stamping bit - PPS-ST (4,5X12)L - 1203534



Stamping bit, for elongated holes: 4.5 x 12 mm

Cutting tool - PPS STANDARD M - 1206175

Accessories

Stamping bit - PPS-ST (5,5X12)L - 1202603



Stamping bit, for elongated holes: 5.5 x 12 mm

Stamping bit - PPS-ST (6,5X15)L - 1202593



Stamping bit, for elongated holes: 6.5 x 15 mm

Stamping bit - PPS-ST (3,5X12)Q - 1203550



Stamping bit, for elongated hole: 3.5 x 12 mm

Stamping bit - PPS-ST (4,5X12)Q - 1203547



Stamping bit, for elongated hole: 4.5 x 12 mm

Stamping bit - PPS-ST (5,5X12)Q - 1203411



Stamping bit, for elongated hole: 5.5 x 12 mm

Cutting tool - PPS STANDARD M - 1206175

Accessories

Stamping bit - PPS-ST (6,5X15)Q - 1203408



Stamping bit, for elongated hole: 6.5 x 15 mm

Stamping bit - PPS-ST (3,8) - 1204892



Stamping bit, for bore holes: 3.8 mm diameter

Stamping bit - PPS-ST (4,3) - 1202616



Stamping bit, for bore holes: 4.3 mm diameter

Stamping bit - PPS-ST (5,3) - 1202629



Stamping bit, for bore holes: 5.3 mm diameter

Stamping bit - PPS-ST (6,4) - 1202632



Stamping bit, for bore holes: 6.4 mm diameter

Cutting tool - PPS STANDARD M - 1206175

Accessories

Stamping bit - PPS-ST (7,0) - 1204889



Stamping bit, for bore holes: 7.0 mm diameter

Stamping bit - PPS-ST (8,4) - 1202726



Stamping bit, for bore holes: 8.4 mm diam

Profile cutters

Workbench - PPS TABLE - 1206285



Workbench, without mounting screws, without bore holes, without DIN-rail cutter, 50 mm thick plywood panel measuring 700 x 1200 mm

Universal tools

Tool - PPS HYDRAULIC CYL - 1208924



Hydraulic cylinder
