

Tool - SF-CCK 9 - 1212525

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Control cabinet keys made of metal for all the usual closures: Two-way key bit 3-5 mm, square 5,6,7-8,9-10 mm, triangle 7,8-9,10-11 mm, special 6 mm

Your advantages

- Universal control cabinet key, with strong chain and snap hook

Key Commercial Data

| | |
|--------------------------------------|---------------|
| Packing unit | 1 pc |
| GTIN | |
| GTIN | 4046356589536 |
| Weight per Piece (excluding packing) | 225.200 g |
| Custom tariff number | 83017000 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|------------|-------|
| Length (b) | 95 mm |
| Width (a) | 95 mm |

General

| | |
|----------|---------------|
| Type | Plug-in |
| Material | Zinc die-cast |
| Weight | 175 g |

Environmental Product Compliance

| | |
|---------------------------|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |
|---------------------------|---|

Drawings

Tool - SF-CCK 9 - 1212525

Schematic diagram



1



2



3



4

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 21043000 |
| eCl@ss 4.1 | 21043000 |
| eCl@ss 5.0 | 21043200 |
| eCl@ss 5.1 | 21050800 |
| eCl@ss 6.0 | 27409200 |
| eCl@ss 7.0 | 27409215 |
| eCl@ss 8.0 | 27409215 |
| eCl@ss 9.0 | 27400638 |

Tool - SF-CCK 9 - 1212525

Classifications

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC000175 |
| ETIM 5.0 | EC000175 |
| ETIM 6.0 | EC000175 |
| ETIM 7.0 | EC000175 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 27111701 |
| UNSPSC 7.0901 | 27111701 |
| UNSPSC 11 | 27111701 |
| UNSPSC 12.01 | 27111701 |
| UNSPSC 13.2 | 46171505 |
| UNSPSC 18.0 | 46171505 |
| UNSPSC 19.0 | 46171505 |
| UNSPSC 20.0 | 46171505 |
| UNSPSC 21.0 | 46171505 |

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

| | | |
|-----|---|--------------------------|
| EAC |  | RU C- DE.AI30.B.01750 |
|-----|---|--------------------------|