

# Mounting set for securing the batteries - BATTERY MOUNTING CASE - 2320458

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Used for mounting batteries that cannot be mounted on DIN rails.




## Product Description

Mounting set, consisting of battery frame for universal wall mounting or surface mounting, 2 x cross dowel (M6) with collar, 2 x screw (M6 x 140), 2 x washer (6.4 x 12), 1 x battery retaining bracket with fixing bracket, and 4 x screw (M3 x 14).



## Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 933131
GTIN	4046356933131
Weight per Piece (excluding packing)	5,410.000 g
Custom tariff number	73269098
Country of origin	Germany

## Technical data

### General

Net weight	5 kg
------------	------

### Dimensions

Width	464 mm
Height	201 mm
Depth	205 mm

### Standards and Regulations

Shock	IEC 60068-2-27
Vibration (operation)	DNV GL

# Mounting set for securing the batteries - BATTERY MOUNTING CASE - 2320458

## Classifications

### eCl@ss

eCl@ss 4.0	27378000
eCl@ss 4.1	27378000
eCl@ss 5.0	27379100
eCl@ss 5.1	27379100
eCl@ss 6.0	27379200
eCl@ss 7.0	27379201
eCl@ss 8.0	27059290
eCl@ss 9.0	27059290

### ETIM

ETIM 4.0	EC002498
ETIM 5.0	EC002498
ETIM 6.0	EC002839
ETIM 7.0	EC002839

### UNSPSC

UNSPSC 13.2	39121421
UNSPSC 18.0	26111710
UNSPSC 19.0	26111710
UNSPSC 20.0	26111710
UNSPSC 21.0	26111710

## Approvals

### Approvals

---

Approvals


DNV GL / BV / LR / ABS

---

### Ex Approvals

---

### Approval details


DNV GL		<a href="https://approvalfinder.dnvgl.com/">https://approvalfinder.dnvgl.com/</a>	TAA0000265
Nominal voltage UN	500 V		
Nominal current IN	41 A		

# Mounting set for securing the batteries - BATTERY MOUNTING CASE - 2320458

## Approvals

mm²/AWG/kcmil	6
---------------	---

BV		<a href="http://www.veristar.com/portal/veristarinfo/generalinfo/approved/approvedProducts/equipmentAndMaterials">http://www.veristar.com/portal/veristarinfo/generalinfo/approved/approvedProducts/equipmentAndMaterials</a>	41516/A0 BV
----	---	---	-------------

LR		<a href="http://www.lr.org/en">http://www.lr.org/en</a>	17/20032
----	---	---	----------

ABS	<a href="http://www.eagle.org/eagleExternalPortalWEB/">http://www.eagle.org/eagleExternalPortalWEB/</a>	15-GD1438179-PDA
-----	---	------------------

## Accessories

### Accessories

#### Battery unit

Energy storage - UPS-BAT/VRLA-WTR/24DC/26AH - 2320429



Energy storage device, lead AGM, VRLA technology, 24 V DC, 26 Ah, tool-free battery replacement, automatic detection, and communication with QUINT UPS-IQ

Energy storage - UPS-BAT/VRLA/24DC/38AH - 2320335



Energy storage device, lead AGM, VRLA technology, 24 V DC, 38 Ah, automatic detection, and communication with QUINT UPS-IQ