


PRODUCT-DETAILS

XT3D 250 3p F F

XT3D 250 3p F F



General Information

Extended Product Type	XT3D 250 3p F F
Product ID	1SDA068210R1
EAN	8015644021061
Catalog Description	XT3D 250 3p F F
Long Description	SWITCH-DISCONNECTOR TMAX XT3D 250 FIXED THREE-POLE WITH FRONT TERMINALS

Ordering

EAN	8015644021061
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

Dimensions

Product Net Width	105 mm
Product Net Height	150 mm
Product Net Depth / Length	70 mm
Product Net Weight	1.566 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	155 mm
Package Level 1 Height	190 mm
Package Level 1 Depth / Length	155 mm
Package Level 1 Gross Weight	1.648 kg
Package Level 1 EAN	8015644021061

Additional Information

Electrical Durability	120 cycles per hour 8000 cycle
Mechanical Durability	Nr. Operations 240 cycles per hour Nr. Operations 25000 cycle
Number of Poles	3
Opening Time	CB with SOR 15 ms CB with UVR 15 ms
Order Multiple	1 piece
Product Main Type	SACE Tmax XT
Product Name	Lasttrennschalter
Product Type	SD
Rated Frequency (f)	50 / 60 Hz
Rated Impulse Withstand Voltage (U _{imp})	8 kV
Rated Insulation Voltage (U _i)	800 V
Rated Operational Voltage	690 V AC 500 V DC
Rated Short-time Withstand Current (I _{cw})	for 1 s 3 kA
Rated Uninterrupted Current (I _u)	250 A
Standards	IEC
Sub-type	XT3
Terminal Connection Type	Fixed Circuit-Breakers Front
Version	F

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC210100D0204 1SDC210099D0204
Declaration of Conformity - CE	9AKK106713A5530
Environmental Information	1SDL000190R0001
Instructions and Manuals	1SDH000720R0001

Classifications

ETIM 4	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6	EC000216 - Switch disconnecter
ETIM 7	EC000216 - Switch disconnecter
Object Classification Code	Q
UNSPSC	39120000

Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax XT

