

Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

USB-C Cable (M/M) - USB 3.1, Gen 1 (5 Gbps), Thunderbolt 3 Compatible, 3 ft.

MODEL NUMBER: U420-003



Connect two devices with USB Type-C (USB-C) connectors, such as smartphones, tablets, Ultrabooks and computers.

Description

The U420-003 USB 3.1 Gen 1 Cable connects two devices with USB-C connectors—such as smartphones, tablets, Ultrabooks and computers—or a USB-C device to a wall charger with a USB-C port. This 3-foot cable supports data transfer speeds up to 5 Gbps and power output up to 3A for fast charging of mobile devices. Unlike traditional USB cables that can be attached only one way, the reversible USB-C male connectors plug into a USB port in either direction for fast, fumble-free connection every time. Superior foil shielding provides reliable, error-free data communication. Nickel-plated molded end connectors and gold-plated copper contacts ensure superior conductivity and long life. Slim form supports evolving design trends toward smaller devices. Backward compatible with previous USB generations.

Features

Supports USB 3.1 Gen 1

- Data transfer speeds up to 5 Gbps—10 times faster than USB 2.0
- Power output up to 3A—perfect for fast charging of most mobile devices
- Backward-compatible with previous USB generations

USB Type-C Male Connector

- Fumble-free reversible plug ensures fast, easy connection every time
- Small enough for a smartphone or tablet, yet powerful enough for a laptop, Ultrabook, or computer

Premium Construction

 Gold-plated copper contacts and nickel-plated molded ends provide a lifetime of heavy use and superior conductivity

Highlights

- Connects two USB-C devices
- Supports USB 3.1 Gen 1 data transfer speeds up to 5 Gbps
- Provides power output up to 3A
- Features reversible USB Type-C male plugs on both ends

System Requirements

• Devices with a USB Type-C port

Package Includes

U420-003 USB 3.1 Gen 1 (5
 Gbps) Cable, USB Type-C
 (USB-C) M/M, 3 ft.



- Superior foil shielding offers reliable, error-free data communication
- Slim, sleek design tailored for emerging design trends toward smaller devices

Specifications

OVERVIEW		
UPC Code	037332189257	
INPUT		
Cable Length (ft.)	3	
Cable Length (m)	0.9	
Cable Length (in.)	36	
PHYSICAL		
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	4.5MM	
Color	Black	
Material of Construction	PVC	
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27	
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50	
Shipping Weight (kg)	0.06	
Shipping Weight (lbs.)	0.13	
ENVIRONMENTAL		
Operating Temperature Range	14 to 140 F (-10 to 60 C)	
Storage Temperature Range	-4 to 185 F (-20 to 85 C)	
Relative Humidity	10% to 85%, Non-Condensing	
CONNECTIONS		
Side A - Connector 1	USB C (MALE)	
Side B - Connector 1	USB C (MALE)	
Connector Plating	Nickel	
Contact Plating	Gold	
FEATURES & SPECIFICATIONS		
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)	
Technology	USB 3.1 (Gen 1); USB	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies