

## 4-Port USB-C Hub with Power Delivery, USB-C to 4x USB-A Ports, USB 3.0, White

MODEL NUMBER: U460-004-4A-C



Adds USB-A and USB-C PD charging ports to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

### Description

The U460-004-4A-C USB 3.1 Gen 1 USB-C Portable Hub expands the potential of your tablet, laptop, MacBook, Chromebook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals and powering and charging a PD Charging-compliant mobile device—all at the same time.

The plug-and-play U460-004-4A-C requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Four USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer, and the dedicated BC 1.2-compliant one provides up to 1.5A for charging smartphones and other mobile devices. All ports support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook or Chromebook) connected to the U460-004-4A-C. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 20V 3A (60W).

### Features

**Turn Your Device's USB-C Port into a Multiport Workstation** Ideal for adding USB peripherals and powering and charging a PD Charging-compliant mobile device simultaneously  
Plug-and-play operation with no software, drivers or external power required  
About the size of a credit card for easy carrying in a pocket, purse or laptop bag

**Connect USB Peripherals** 4 USB-A ports accept flash drives, mice, keyboards, printers and other USB peripherals  
BC 1.2-compliant USB-A port provides up to 1.5A for charging mobile devices  
Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps  
Backward compatible with USB 2.0 and USB 1.1

**Charge a Connected Device** USB-C PD port connects to wall charger to power and charge the connected PD Charging-compliant USB-C/Thunderbolt 3 device  
Supports power input up to 20V 3A (60W)

**Built-In Cable with Reversible USB-C Connector** Fumble-free reversible USB-C plug connects in either direction for quick connection every time

### Highlights

- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- USB-C PD charging port supports power input up to 20V 3A (60W)
- BC 1.2-compliant USB-A port provides up to 1.5A for charging devices
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

### System Requirements

- Source device with USB-C or Thunderbolt 3 port

### Package Includes

- U460-004-4A-C USB 3.1 Gen 1 USB-C Portable Hub
- Owner's manual



## Specifications

OVERVIEW	
UPC Code	037332193773
OUTPUT	
Charging Ports / Amps	0.9A; 1.5A; 3A
Charging Watts	60
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (1.2 Port)	Yes
PHYSICAL	
Cable Jacket Rating	VW-1
Color	White
Material of Construction	ABS, PVC
Shipping Dimensions (hwd / in.)	0.90 x 3.90 x 5.60
Shipping Weight (lbs.)	0.20
Unit Dimensions (hwd / in.)	0.43 x 3.7 x 1.6
Unit Packaging Type	Box
Unit Weight (kg)	0.05
Unit Weight (lbs.)	0.1
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Relative Humidity	10% to 90% RH, Non-Condensing
BTUs	7.5 BTU/Hr
Power Consumption (Watts)	2.2



Power Provided to Connected Device(s)	Up to 20V 3A (60W) Input (USB-C), 5V 1.5A (7.5W) Output BC 1.2 USB port, 5V 0.9A (4.5W) Output per USB port
<b>CONNECTIONS</b>	
Ports	5
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(4) USB 3.0 A (FEMALE)
Side B - Connector 2	USB Type-C (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	No
USB Power Delivery (PD) Charging Support	Yes
Technology	USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); PD Charging
<b>CERTIFICATIONS</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>