

Portable Power Expansion Hub for Apple USB-C Power Adapter - 4 Ports (3 USB-A, 1 USB-C 45W)

MODEL NUMBER: U280-A04-A3C1



Compact hub expands your Apple USB-C PD Charger from one to 4 charging ports, allowing you to charge 4 mobile devices at the same time.

Features

All-in-One Charger Adapter Allows You to Charge up to 4 Devices at the Same Time

This portable charger expansion hub attaches to the 61W or 87W AC wall charger that came with your Apple MacBook Pro to expand the number of charging ports from one to four. A white LED indicates sufficient charging power is available for your devices.

Connect Your Devices to a USB-C Port and 3 USB-A Ports for Pure Charging

The USB-C PD 3.0 port produces a maximum power output up to 20V 2.25A (45W). A USB-A Quick Charge 3.0 port offers charging speeds up to four times faster than conventional USB wall chargers for compatible devices. The remaining two USB-A BC 1.2 ports supply up to 5V 2.4A for charging. All four ports can be utilized simultaneously to keep your MacBook, Chromebook, smartphones and tablets ready to use.

Dedicated to Keeping Your Expensive Gadgets Safe

The U280-A04-A3C1 protects your connected devices against overcharging, overheating, overvoltage and short circuits. The unit's non-slip grip padding provides a secure connection to the power adapter. It is colored white and molded to integrate perfectly with the Apple charger and help you reduce unsightly cable clutter.

Highlights

- Expands an Apple MacBook Pro 61W/87W PD charger to 3 USB-A and 1 USB-C ports
- USB-C PD 3.0 port features maximum power output up to 20V 2.25A (45W)
- USB-A QC 3.0 port charges up to 4 times faster than conventional USB wall chargers
- Dual USB-A BC 1.2 ports supply up to 5V 2.4A power for keeping devices at capacity
- Protects connected devices against overcharging, overheating and short circuits

Applications

- Charge up to 4 devices at the same time, including iPhones, iPads, MacBooks, Chromebooks, Android smartphones and Windows tablets
- Carry in your laptop bag or backpack, rather than multiple chargers, for charging all your devices at once when away from home or office

Package Includes

- U280-A04-A3C1 Portable Power Expansion Hub, 4 Ports
- Quick Start Guide

Specifications

OVERVIEW



UPC Code	037332247469
OUTPUT	
Charging Ports / Amps	(1) 1.5A; (1) 2.25A; (2) 2.4A
Output Capacity	USB-C: 45W (20V/2.25A), QC3.0: 18W (12V/1.5A), USB-A: 12W (5V/2.4A)
Charging Method	USB
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Power (White)
PHYSICAL	
Color	White
Material of Construction	Plastic
Unit Dimensions (hwd / in.)	2.91 x 2.32 x 1.35
Unit Packaging Type	Box
Unit Weight (kg)	0.13
Unit Weight (lbs.)	0.29
ENVIRONMENTAL	
Operating Temperature Range	41 to 95°F (5 to 35°C)
Storage Temperature Range	-4 to 122°F (-20 to 50°C)
Relative Humidity	20% to 80% RH, Non-Condensing
CONNECTIONS	
Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (FEMALE)
Side B - Connector 2	(3) USB A (FEMALE)
FEATURES & SPECIFICATIONS	
Driver Required	No
USB Power Delivery (PD) Charging Support	Yes
Quick Charge Compliant	3.0
Technology	USB
USB Power Delivery (PD) Charging Specification	3.0
CERTIFICATIONS	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>