

## 4-Port USB-C Hub with Self-Storing Cable and Power Delivery, 2x USB-A, 2x USB-C, 100W PD 3.0, USB 3.0

MODEL NUMBER: U460-T04-2A2C-1



Adds a USB-C, a USB-C Power Delivery and 2 USB-A ports to the USB-C or Thunderbolt 3 port on your MacBook, PC, tablet or smartphone.

### Features

**USB-C 3.1 Hub Connects 4 USB Peripherals to Your MacBook or Chromebook**This USB-C hub allows you to connect up to four USB peripherals to your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC. Not only can you expand the potential of your device by connecting USB peripherals, such as an external hard drive, flash drive, power meter and printer, but you can also power and fast-charge the device through the USB-C Power Delivery (PD) 3.0 port.

**PD Charging Port Charges the Connected Device via AC Wall Charger**The USB-C PD charging port provides power output up to 5 amps (100 watts), which is more than sufficient for charging and powering the connected device, such as a MacBook or Chromebook. Just connect the device's AC wall charger to the USB-C PD port to enjoy fast data transfer speeds up to 5 Gbps.

**Connects USB Peripherals and Transfers Data at Fast USB 3.1 Gen 1 Speeds**In addition to accepting USB peripherals, the dual USB-A 3.0 ports provide up to 0.9 amps each for charging and powering mobile devices. The USB-C data port provides up to 1.5A for charging devices. All four USB ports transfer data at speeds up to 5 Gbps, which is 10 times faster than USB 2.0. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

**Self-Storing USB-C Cable Connects in Either Direction**Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time. The six-inch cable wraps into the adapter when not in use, making the unit easy to carry in a briefcase or laptop bag for connecting on the go.

**Ready to Use Right Out of the Package**The plug-and-play USB Type-C hub is specifically designed for use with the MacBook, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software, drivers or external power.

### Highlights

- USB-C 3.1 Type-C hub is compatible with all USB-C and Thunderbolt 3 devices
- Power Delivery cable provides 5A (100W) power output for charging connected device
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

### Applications

- Charge and power a MacBook, Chromebook, tablet or other USB-C or Thunderbolt 3 device
- Connect up to 4 USB peripherals, such as an external hard drive, flash drive, power meter and printer

### System Requirements

- Device with USB-C or Thunderbolt 3 port (USB 3.1 port needed to achieve USB 3.1 speeds)

### Package Includes

- U460-T04-2A2C-1 USB 3.1 C Hub, 5 Gbps, Black
- Owner's manual



## Specifications

OVERVIEW	
UPC Code	037332232793
OUTPUT	
Charging Ports / Amps	0.9A; 1.5A; 5A
Charging Watts	100
INPUT	
Built-In Cable Length (in.)	6
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (1.2 Port)	Yes
PHYSICAL	
Cable Jacket Rating	VW-1
Color	Black
Material of Construction	ABS, PVC
Shipping Dimensions (hwd / in.)	0.00 x 0.00 x 0.00
Shipping Weight (lbs.)	0.00
Unit Dimensions (hwd / in.)	0.55 x 3 x 1.7
Unit Packaging Type	Box
Unit Weight (kg)	0.03
Unit Weight (lbs.)	0.07
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	23 TO 158 F (-5 TO 70 C)
Operating Humidity Range	5% TO 85% RH, NON-CONDENSING
Storage Humidity Range	5% TO 90% RH, NON-CONDENSING
Power Provided to Connected Device(s)	100W (2A 5V) PD 3.0 Charging Port, BC 1.2 Charging Port



<b>CONNECTIONS</b>	
Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(2) USB 3.0 A (FEMALE)
Side B - Connector 2	(2) USB C (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	Yes
USB Power Delivery (PD) Charging Support	Yes
Technology	USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); PD Charging
USB Power Delivery (PD) Charging Specification	3.0
<b>CERTIFICATIONS</b>	
Certifications	Tested to RoHS, CE, FCC
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>