

USB-C to USB-A Cable (M/M), USB 3.1 Gen 1 (5 Gbps), Thunderbolt 3 Compatible, 3 ft.

MODEL NUMBER: **U428-003**



Connect a USB Type-C (USB-C) device to the USB Type-A port on your tablet, computer or USB charger.

Description

The U428-003 USB 3.1 Gen 1 Cable connects a USB Type-C (USB-C) device to the USB Type-A port on your tablet, computer, or USB charger. The 3-foot cable supports data transfer speeds up to 5 Gbps. Unlike traditional USB cables that can be attached only one way, the reversible USB Type-C male connector plugs into a USB port in either direction for fast, fumble-free connection every time. Superior foil shielding provides reliable, error-free data communication. Nickel-plated molded end connectors and gold-plated copper contacts ensure superior conductivity and long life. Slim form supports evolving design trends toward smaller devices. Backward-compatible with USB 3.0 devices.

Features

Supports USB 3.1 Gen 1 Data transfer speeds up to 5 Gbps—10 times faster than USB 2.0
 Uses same Type-A male connector as USB 3.0 devices
USB Type-C (USB-C) Male Connector Fumble-free reversible plug ensures fast, easy connection every time
 Powerful enough for smartphones, tablets, computers and other larger platforms
Premium Construction Gold-plated copper contacts and nickel-plated molded ends provide a lifetime of heavy use and superior conductivity
 Superior foil shielding offers reliable, error-free data communication
 Slim, sleek design tailored for emerging design trends toward smaller devices

Specifications

OVERVIEW	
UPC Code	037332189288
INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.9

Highlights

- Connects a USB Type-C (USB-C) device to the USB Type-A port on your tablet, computer, or USB charger
- Supports USB 3.1 Gen 1 data transfer speeds up to 5 Gbps
- Features reversible USB Type-C male plug on one end
- Works with USB 3.0 devices

System Requirements

- Device with USB Type-C (USB-C) port
- Device with USB Type-A port

Package Includes

- U428-003 USB 3.1 Gen 1 (5 Gbps) Cable, USB Type-C (USB-C) to USB Type-A M/M, 3 ft.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (in.)	36
PHYSICAL	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5MM
Color	Black
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.06
Shipping Weight (lbs.)	0.13
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	10% to 85%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB 3.0 A (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)
Technology	USB 3.1 (Gen 1); USB
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>