

USB-C to USB-A Cable (M/M), USB 3.1 Gen 2 (10 Gbps), USB-IF Certified, Thunderbolt 3 Compatible, 3 ft.

MODEL NUMBER: U428-C03-G2











USB-C 3.1 to USB-A cable connects a smartphone or other USB-C device to the USB-A port on your computer, wall charger or car charger.

Features

USB Type-C to USB Type-A Cable Connects a USB-C Mobile Device to Your ComputerThis three-foot USB-C 3.1 to USB-A cable allows you to connect a device with a USB-C or Thunderbolt 3 port to a USB-enabled computer, charger, hard drive or other peripheral for the purpose of charging, powering, syncing or transferring data. It is compatible with any device with a USB-C or Thunderbolt 3 port, including tablets, smartphones, MacBooks, Ultrabooks and Chromebooks.

PD Charging Cable Charges Devices and Transfers Data at Lightning-Fast USB 3.1 Gen 2
SpeedsThe USB-C to USB-A cable supports USB 3.1 Gen 2 data transfer rates up to 10 Gbps, which is twice as fast as USB 3.1 Gen 1. The Power Delivery cable also provides power output up to 3 amps (60 watts), which is more than sufficient for charging, syncing and powering compatible devices. The cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

Reversible USB-C Connector Attaches in Either DirectionUnlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

USB-IF Certification Ensures Rigorous Testing and Top-of-the-Line PerformanceThis USB Type-C to USB Type-A cable meets the high standards of USB-IF (USB Implementers Forum, Inc.), a non-profit organization consisting of companies that developed the USB specification. Receiving USB-IF certification means the U428-C03-G2 meets the industry's highest environmental, mechanical and electrical standards. It operates with your USB peripherals, adapters and cables with top efficiency and safety.

Highlights

- Certified by USB-IF to ensure highest-grade construction and performance
- Supports USB 3.1 Gen 2 speeds up to 10 Gbps to ensure lightning-fast data transfers
- Power Delivery cable provides 3A (60W) power output for charging mobile devices
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- USB-C to USB-A cable is compatible with all USB-C and Thunderbolt 3 devices

Applications

- Charge and sync a USB-C or Thunderbolt 3 mobile device from a USB-A wall charger up to 3 ft. away
- Connect a printer or scanner to the USB-C port on your computer or laptop
- Transfer data between an external hard drive or flash drive and your computer or laptop
- Connect your computer or laptop to a docking station or hub with a USB-C or Thunderbolt 3 port

System Requirements

- Device with a USB-C or Thunderbolt 3 port (USB 3.1 Gen 2 compatibility required to achieve USB 3.1 Gen 2 speeds)
- Device with a USB-A port



Package Includes

 U428-C03-G2 USB Type-C to USB Type-A Cable, M/M, USB-IF Certified, 3 ft.

Specifications

-		
OVERVIEW		
UPC Code	037332215031	
INPUT		
Cable Length (ft.)	3	
Cable Length (m)	0.9	
Cable Length (in.)	36	
PHYSICAL		
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	4.8 mm	
Color	Black	
Material of Construction	PVC	
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50	
Shipping Weight (kg)	0.03	
Shipping Weight (lbs.)	0.07	
Unit Packaging Type	Polybag	
ENVIRONMENTAL		
Operating Temperature Range	14 to 140 F (-10 to 60 C)	
Storage Temperature Range	-4 to 158 F (-20 to 70 C)	
Relative Humidity	10% to 85%, Non-Condensing	
CONNECTIONS		
Side A - Connector 1	USB 3.0 A (MALE)	
Side B - Connector 1	USB C (MALE)	
Connector Plating	Nickel	
Contact Plating	Gold	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

FEATURES & SPECIFICATIONS		
USB Specification	USB 3.1 Gen 2 (up to 10 Gbps)	
Technology	USB; USB 3.1 (Gen 2)	
CERTIFICATIONS		
Certifications	Tested to CE, FCC, ROHS, REACH, USB-IF	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies