

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → Solution Series

## General Information

<b>Extended Product Type:</b>	BRT80A
<b>Product ID:</b>	1SNA179534R2200
<b>EAN:</b>	3472591795349
<b>Catalog Description:</b>	BRT80A Distribution Terminal Blocks - Feed-through - Four poles
<b>Long Description:</b>	BRT80A Distribution Terminal Blocks - Feed-through - Four poles , 4 x 9 connections , 80A MaxCurrent, 88mm Spacing TH 35-7.5, TH 35-15 Rail.

## Ordering

<b>Color:</b>	grey
<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85369010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC160001C0207-CH-G Distribution terminals
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-G Distribution terminals

## Dimensions

<b>Product Net Width:</b>	88 mm
<b>Product Net Height:</b>	85 mm
<b>Product Net Depth / Length:</b>	45 mm
<b>Product Net Weight:</b>	250 g

## Technical

<b>Connection Type:</b>	Screw clamp
<b>Function:</b>	Distribution
<b>Number of Levels:</b>	3
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

## Environmental

<b>Ambient Air Temperature:</b>	Operation -30 ... +90 °C Storage -30 ... +100 °C
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	1SND225008U1000
--	-----------------

<b>EAC Certificate:</b>	1SND161009A1100
<b>Environmental Information:</b>	1SND220046E1002
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-G Distribution terminals
<b>RMRS Certificate:</b>	1SND161007A1101
<b>RoHS Information:</b>	1SND230013F0202

## Classifications

<b>Object Classification Code:</b>	X
<b>ETIM 4:</b>	EC001894 - Distributor assembly terminal blocks
<b>ETIM 5:</b>	EC001894 - Distributor assembly terminal blocks
<b>ETIM 6:</b>	EC001894 - Distributor assembly terminal blocks

## Container Information

<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Depth / Length:</b>	88 mm
<b>Package Level 1 Gross Weight:</b>	0.25 kg
<b>Package Level 1 EAN:</b>	3472591795349
<b>Package Level 2 Units:</b>	10 piece
<b>Package Level 3 Units:</b>	100 piece
<b>Product Packing Type:</b>	Box

