

USB-C to USB Micro-B Cable (M/M) - USB 3.1, Gen 1 (5 Gbps), Thunderbolt 3 Compatible, 6 ft.

MODEL NUMBER: U426-006



Connects a smartphone or other USB Micro-B device to your laptop, MacBook, Chromebook or Ultrabook's USB-C or Thunderbolt 3 port.

Features

USB-C to USB Micro-B Cable Connects a USB 3.0 Micro-B Device to Your Computer or TabletThis six-foot USB-C to Micro-B cable allows you to connect your smartphone, external hard drive or other device with a USB Micro-B port to any device with a USB-C or Thunderbolt 3 port, including MacBooks, Ultrabooks and Chromebooks.

PD Charging Cable Charges Devices and Transfers Data at Fast USB 3.1 Gen 1 SpeedsThe USB-C to USB Micro-B cable supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps, which is 10 times faster than USB 2.0. The Power Delivery cable also provides power output up to 3 amps (60 watts), which is more than sufficient for charging, syncing and powering compatible devices. The cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

Reversible USB-C Connector Attaches in Either DirectionUnlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Highlights

- USB-C to Micro-B cable compatible with USB Micro-B, USB-C and Thunderbolt 3 devices
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Power Delivery cable provides 3A (60W) power output for charging mobile devices
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Easy installation with plug-and-play operation—no software required

Applications

- Charge and sync a USB Micro-B mobile device from a USB-C vehicle charger or wall charger up to 6 ft. away
- Transfer data between an external hard drive and your laptop or computer

System Requirements

- Device with a USB-C or Thunderbolt 3 port (USB 3.1 Gen 1 compatibility required to achieve 5 Gbps speeds)
- Device with a USB Micro-B port (USB 3.0 compatibility required to achieve 5 Gbps speeds)

Package Includes

- U426-006 USB Type-C to USB Micro-B Cable, M/M, 6 ft.



Specifications

OVERVIEW	
UPC Code	037332218384
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
PHYSICAL	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5 mm
Color	Black
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.04
Shipping Weight (lbs.)	0.08
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	-40 to 158 F (-40 to 70 C)
Operating Humidity Range	10% to 85%, Non-Condensing
Storage Humidity Range	5% to 90%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB 3.0 MICRO-B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)
Technology	USB 3.1 (Gen 1); USB



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS and REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>