

3 m (9.8 ft.) HDMI to DisplayPort Cable - 4K 30Hz

Product ID: HD2DPMM3M



This 3 m (10ft.) HDMI to DisplayPort cable with USB power lets you connect an HDMI video source, such as your laptop, desktop, Blu-ray™ player, or camera, to a DisplayPort monitor or projector without the need for additional video cables. The adapter cable features male connectors enabling you to connect your video source directly to the display, with no need for additional adapters or cables.

Convenient Connectivity

The active HDMI 1.4 to DisplayPort 1.2 converter cable offers plug-and-play installation, providing a hassle-free setup with no software or drivers to install. The adapter is powered via a USB port, avoiding the need for an extra power adapter.

Astonishing picture quality

With support for 4K at 30Hz, you get a sharp, crisp picture that's richer and more true-to-life than traditional HD, with far greater detail. The HDMI to DisplayPort Adapter cable delivers Ultra HD content to your DisplayPort monitor and supports 7.1 channel surround sound audio.

The HDMI to DisplayPort adapter is backward compatible with 1080p and 1440p displays, which makes it a great accessory to future-proof your existing setup for 4K video.

The Choice of IT Pros Since 1985

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

The HD2DPMM3M is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Use in your boardroom or office workstations for installations requiring 3 meters (9.8 feet) of cable
- Connect your HDMI computer to a DisplayPort monitor
- Viewing video footage from your HDMI source on a DisplayPort monitor

Features

- Provides a convenient plug-and-play solution with no additional cables required
- Active HDMI to DisplayPort conversion transmits high-definition audio and video from your computer to a DP monitor
- Deliver astonishing picture quality with support for video resolutions up to Ultra HD 4K

Hardware	Warranty	2 Years
	Active or Passive Adapter	Active
	Audio	Yes
	AV Input	HDMI - 1.4
	AV Output	DisplayPort
	Chipset ID	MegaChips Technology - STDP2600
Performance	Audio Specifications	DisplayPort - 7.1 Channel Audio
	Maximum Digital Resolutions	3840 x2160
	Supported Resolutions	DisplayPort: 3840x2160 (4K) / 30Hz Additional resolutions and refresh rates may be supported
	Video Revision	HDMI 1.4
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - HDMI (19 pin) Male Input
	Connector B	1 - DisplayPort (20 pin) Male Output
Power	Power Source	USB-Powered
Environmental	Humidity	5~90% RH (Non-condensing)
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-10°C to 55°C (14°F to 131°F)
Physical Characteristics	Color	Black
	Material	Plastic
	Product Height	10.600
	Product Length	118.1 in [300 cm]
	Product Width	20.900
	Weight of Product	200.000
Packaging Information	Package Height	25.000
	Package Length	200.000
	Package Width	218.000
	Shipping (Package) Weight	205.000
What's in the Box	Included in Package	1 - HDMI to DisplayPort Cable

Product appearance and specifications are subject to change without notice.