

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2070190010](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit Family Power Connectors](#)  
**Description:** [Mini-Fit Sigma Sealed Cap for 10 Circuit Plug Housing](#)

**Documents:**

|   |   |
|---|---|
| <a href="#">3D Model</a>  | <a href="#">Packaging Specification 2070180000-PK-000 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                                     | <a href="#">Test Summary 2070170000-TS-000 (PDF)</a>            |
| <a href="#">3D Model (PDF)</a>                                    | <a href="#">Test Summary 2070170001-TS-000 (PDF)</a>            |
| <a href="#">Product Specification 2070170000-PS-000 (PDF)</a>     | <a href="#">RoHS Certificate of Compliance (PDF)</a>            |
| <a href="#">Application Specification 2070170000-AS-000 (PDF)</a> |   |



*Series image - Reference only*

**General**

|                |  |
|----------------|--|
| Product Family | Accessories                                      |
| Series         | <a href="#">207019</a>                           |
| Component Type | Cap  |
| Overview       | <a href="#">Mini-Fit Family Power Connectors</a> |
| Product Name   | Mini-Fit Sigma                                   |
| UPC            | 193264428588                                     |

**Physical**

|                               |                         |
|-------------------------------|-------------------------|
| Circuits (Loaded)             | 10                      |
| Circuits (maximum)            | 10                      |
| Color - Resin                 | Black                   |
| Lock to Mating Part           | Yes                     |
| Material - Resin              | Thermoplastic Elastomer |
| Net Weight                    | 7.800/g                 |
| Packaging Type                | Bag                     |
| Temperature Range - Operating | -40° to +105°C          |

**Material Info**

**Reference - Drawing Numbers**

|                           |                                      |
|---------------------------|--------------------------------------|
| Application Specification | 2070170000-AS-000                    |
| Packaging Specification   | 2070180000-PK-000                    |
| Product Specification     | 2070170000-PS-000                    |
| Sales Drawing             | 2070190000-SD-000                    |
| Test Summary              | 2070170000-TS-000, 2070170001-TS-000 |

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ECHA\_01\_2020 (16  
January 2020

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[207019](#) Series

**Use With**

[Mini-Fit Sigma Sealed Plug Housing](#)  
[2070170010](#)