

PRODUCT-DETAILS

DB200

DB200 Single Mounting Kit



General Information

Extended Product Type	DB200
Product ID	1SAZ401110R0001
EAN	4013614237768
Catalog Description	DB200 Single Mounting Kit
Long Description	DB200 Single mounting kit

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85389099

Popular Downloads

Data Sheet, Technical Information	1SBC100173C0201
Instructions and Manuals	2CDC106089M6801
Dimension Diagram	1SAZ400402F0001

Dimensions

Product Net Width	105 mm
Product Net Height	43 mm

Product Net Depth / Length	40 mm
Product Net Weight	0.225 kg

Technical

Rated Operational Voltage	Main Circuit 690 V AC
Rated Frequency (f)	Main Circuit 50 Hz Main Circuit 60 Hz
Rated Impulse Withstand Voltage (U _{imp})	Main Circuit 6 kV
Rated Insulation Voltage (U _i)	690 V
Number of Poles	3
Pollution Degree	3
Connecting Capacity Main Circuit	Rigid or Flexible with Cable Lug 1x 25 ... 120 mm ² Hole Diameter >10 mm
Tightening Torque	Main Circuit 25 N·m
Suitable For	TA110DU TA200DU
Standards	CSA 22.2 No. 14 IEC/EN 60947-1 IEC/EN 60947-4-1 UL 508

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V AC
Connecting Capacity Main Circuit UL/CSA	Flexible 1x 4 ... 0000 AWG

Environmental

Ambient Air Temperature	Storage -40 ... +70 °C Operation -25 ... +55 °C
RoHS Status	Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

ABS Certificate	No Certificate Needed
BV Certificate	NoCerNee
cUL Certificate	cUL_E48139
Declaration of Conformity - CE	1SAD938517-0043
DNV Certificate	No Certificate Needed
GL Certificate	No Certificate Needed
GOST Certificate	1SAA941000-2704
Instructions and Manuals	2CDC106089M6801
LR Certificate	No Certificate Needed
RINA Certificate	No Certificate Needed
RMRS Certificate	No Certificate Needed
RoHS Information	1SAD938514-0043
UL Certificate	UL_E48139

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	92 mm
Package Level 1 Height	109 mm
Package Level 1 Depth / Length	61 mm
Package Level 1 Gross Weight	0.245 kg
Package Level 1 EAN	4013614237768
Package Level 2 Units	24 piece
Package Level 2 Width	280 mm
Package Level 2 Height	210 mm
Package Level 2 Depth / Length	395 mm
Package Level 2 Gross Weight	8.786 kg
Package Level 2 EAN	4013614494185

Classifications

Object Classification Code	Q
ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 5	EC002498 - Accessories for low-voltage switch technology
ETIM 6	EC002498 - Accessories for low-voltage switch technology
ETIM 7	EC002498 - Accessories for low-voltage switch technology
eClass	7.0 27379201
E-Number (Sweden)	3229006

Categories

Low Voltage Products and Systems → Control Products → Contactors → Thermal Overload Relays Accessories

