



NEXUS



Angled inline and colour coded terminals



Removable flex outlet



Screw covers for sleek appearance




Modern slimline neon inlaid red rocker indicator



Modern slimline profile



All light switches
 10AX rated



Large terminals
 Spare screw covers
 Retained screws



Retrofit spacer for
 easy installation
 during rewires



10AX PLATE SWITCHES

| Code | Description |
|------|----------------------------------|
| 811 | 1 Gang, 1 Way 10AX Switch |
| 812 | 1 Gang, 2 Way 10 AX Switch |
| 813 | Intermediate 10 AX Switch |
| 814 | Bell Push |
| 815 | 3 Pole Fan Isolator 10 AX Switch |
| 842 | 2 Gang, 2 Way 10 AX Switch |
| 843 | 3 Gang, 2 Way 10 AX Switch |
| 844 | 4 Gang, 2 Way 10 AX Switch |
| 846 | 6 Gang, 2 Way 10 AX Switch |

Manufactured to BS EN 60669-1.

20A SWITCHES

| Code | Description |
|-------|--|
| 830 | 20A DP Switch |
| 831 | 20A DP Switch with Neon |
| 832 | 20A DP Switch with Flex Outlet |
| 833 | 20A DP Switch with Neon and Flex Outlet |
| 832WH | 20A DP Switch, marked Water Heater with Flex Outlet |
| 833WH | 20A DP Switch, marked Water Heater with Neon and F/O |

Manufactured to BS EN 60669-1.

45A SWITCHES

| Code | Description |
|------|---|
| 870 | 45A DP Cooker Control Unit with 13A Socket and Neon |
| 871 | 45A DP Cooker Control Unit with 13A Socket |
| 872 | 45A DP Switch with Neon Large Plate |
| 873 | 45A DP Switch Large Plate |
| 874 | 45A DP Switch with Neon Single Plate |
| 875 | 45A DP Switch Single Plate |

Manufactured to BS 4177 and BS EN 60669-1. All units supplied with spacer plates.

45 AMP COOKER OUTLET

| Code | Description |
|------|------------------------------------|
| 879 | 45A Flex Outlet Plate Bottom Entry |

Manufactured to BS 5733.



13 AMP SOCKET OUTLETS

| Code | Description |
|-------|---------------------------------|
| 821SP | 1 Gang 13A Single Pole Switched |
| 821DP | 1 Gang 13A Double Pole Switched |
| 822SP | 2 Gang 13A Single Pole Switched |
| 822DP | 2 Gang 13A Double Pole Switched |
| 823 | 1 Gang 13A Unswitched |
| 824 | 2 Gang 13A Unswitched |
| 825 | 1 Gang 13A Switched With Neon |
| 826 | 2 Gang 13A Switched With Neon |

Manufactured to BS 1363 part 2.

ROUND PIN SOCKET OUTLETS

| Code | Description |
|------|---------------------------------------|
| 828 | 1 Gang 2A Unswitched Socket Round Pin |
| 829 | 1 Gang 5A Unswitched Socket Round Pin |
| 899 | 1 Gang 15A Switched Socket Round Pin |

Manufactured to BS 546.

13 AMP FUSED CONNECTION UNITS

| Code | Description |
|------|------------------------------------|
| 850 | 13A Switched and Fused |
| 852 | 13A Switched and Fused with Neon |
| 854 | 13A Unswitched and Fused |
| 856 | 13A Unswitched and Fused with Neon |

Manufactured to BS 1363 part 4.

13 AMP FUSED CONNECTION UNITS WITH FLEX

| Code | Description |
|------|--|
| 851 | 13A Switched and Fused with Flex Outlet |
| 853 | 13A Switched and Fused with Neon and Flex Outlet |
| 855 | 13A Unswitched and Fused with Flex Outlet |
| 857 | 13A Unswitched and Fused with Neon and Flex Outlet |

Manufactured to BS 1363 part 4.

25 AMP FLEX OUTLET PLATE


| Code | Description |
|------|------------------------------------|
| 858 | 25A Flex Outlet Plate Bottom Entry |

Manufactured to BS 5733.

SHAVER SOCKET

| Code | Description |
|------|-------------------------------------|
| 820 | 115/230V Dual Voltage Shaver Socket |

Manufactured to BS EN 61558-1.



CO-AXIAL, SATELLITE AND TRIPLEX OUT

| Code | Description |
|------|--|
| 860 | 1 Gang Co-axial Socket |
| 861 | 2 Gang Co-axial Socket |
| 862 | 1 Gang Isolated Co-axial Socket |
| 863 | 2 Gang Isolated Co-axial Socket |
| 864 | 1 Gang Satellite Socket |
| 865 | 2 Gang Satellite and Co-axial Socket |
| 866 | 2 Gang Diplex TV/FM |
| 867 | 3 Gang TV/FM/SAT Triplex |
| 868 | Triplex with BT Outlet and Co Axial Return |

Manufactured to BS 3041 and BS 5733 where applicable.

TELEPHONE & DATA OUTLETS

| Code | Description |
|---------|--------------------------------|
| 8BTM/1 | 1 Gang Telephone Socket Master |
| 8BTM/2 | 2 Gang Telephone Socket Master |
| 8BTS/1 | 1 Gang Telephone Socket Slave |
| 8BTS/2 | 2 Gang Telephone Socket Slave |
| 8RJ45/1 | 1 Gang RJ45 Data Outlet Socket |
| 8RJ45/2 | 2 Gang RJ45 Data Outlet Socket |
| 8RJ11/1 | 1 Gang RJ11 Telephone Socket |
| 8RJ11/2 | 2 Gang RJ11 Telephone Socket |

Manufactured to BS 6312 part 2 where applicable.

Modules available to make up any combination of RJ11, BT and RJ45 outlets

DIMMERS

| Code | Description |
|------|------------------------|
| 881 | 1 Gang 2 Way Push 400W |
| 882 | 2 Gang 2 Way Push 400W |
| 883 | 3 Gang 2 Way Push 400W |
| 884 | 4 Gang 2 Way Push 400W |

Manufactured to BS EN 60669. All dimmers are supplied with spacer plates.

SURFACE BOXES AND BLANK PLATES

| Code | Description |
|------|--------------------------------|
| 817 | 1 Gang 10mm Square Spacer |
| 818 | 2 Gang 10mm Rectangular Spacer |
| 891 | 1 Gang Surface Box 32mm |
| 892 | 2 Gang Surface Box 32mm |
| 893 | 1 Gang Surface Box 19mm |
| 894 | 1 Gang Blank-plate |
| 895 | 2 Gang Blank-plate |
| 896 | Dual Surface Patress Box 37mm |
| 877 | 1 Gang Surface Box 50mm |
| 878 | 2 Gang Surface Box 50mm |

Manufactured to BS5733.