

acer



PROJECTING THE FUTURE BUSINESS OF

Acer P1155

4,000 lumens brightness

Acer Bluelight Shield

Acer LumiSense

20,000:1 Dynamic Black



Product Specifications

Model name	P1155
Projection system	DLP™
Resolution	SVGA (800 x 600) Maximum WUXGA (1,920 x 1,200)
Brightness	4,000 ANSI Lumens (Standard), 3,200 ANSI Lumens (ECO) (Compliant with ISO 21118 standard)
Aspect ratio	4:3 (Native), 16:9 (Supported)
Contrast ratio	Dynamic Black 20,000:1
Throw ratio	1.96 ~ 2.15 (50" @ 2 m)
Projection lens	F = 2.56 ~ 2.68, f = 22.0 mm ~ 24.1 mm Manual Zoom and Manual Focus
Keystone correction	+/-40° (Vertical, Manual & Auto)
Lamp life	5,000 Hours (Standard), 10,000 Hours (ECO), 15,000 Hours (ExtremeEco)
Noise level	34 dBA (Standard), 29 dBA (ECO)
Input interface	Analog RGB/Component Video (D-sub) x 2 Composite Video (RCA) x 1 HDMI (Video, Audio, HDCP) x 1 HDMI/MHL (Video, Audio, HDCPI) x 1 PC Audio (Stereo mini jack) x 1
Output interface	Analog RGB (D-sub) x 1 PC Audio (Stereo mini jack) x 1 DC Out (5V/1A, USB Type A) x 1
Control	USB (mini-B) x 1 RS-232 (mini DIN) x 1
Dimensions	299.5 x 220 x 105.1 mm (11.8" x 8.7" x 4.1", with feet)
Weight	2.4 Kg (5.29 lbs)

Feature Highlights

Expressive display

- SVGA (800 x 600)
- 4,000 ANSI lumens
- Dynamic Black 20,000:1
- Acer BlueLightShield
- Acer LumiSense
- Acer ColorBoost3D
- Acer ColorSafe II
- HDMI 3D

Enhanced usability

- 3W built-in speaker
- Wireless Projection¹
- AC power on

Installation flexibility

- Auto Keystone correction
- Auto ceiling-mounted correction
- Top-loading lamp


Eco-friendly functionality

- Acer EcoProjection
- Lamp life up to 15,000 hours in ExtremeEco mode

1 - Optional Acer WirelessCAST or Acer WirelessHD-Kit is required.

P1155

- Part Number: MR.JSH11.001
- EAN Code: 4710180759389



Optional Accessory



WirelessCAS
T

P/N: MC.JKY11.007
EAN: 4713147653638



WirelessHD-Kit
MWIHD1

P/N: MC.JKY11.009
EAN: 4713147715251



WirelessMirror
HWA1

P/N: MC.JQC11.008
EAN: 4713883764520



Ceiling Mount
CM-01S

P/N: MC.JLC11.002
EAN: 4713147892877



Ceiling Mount
CM-02S

P/N: MC.JLC11.003
EAN: 4713147892884



3D Glasses
E4W

P/N: MC.JFZ11.00B
EAN: 4713147532261



BlueLightShield™

Acer BlueLight Shield

Acer BlueLight shield allows users to lower levels of blue light to lessen the negative effects of blue light exposure. There are three levels of filter in projector suitable for different scenario. Each level also contains dynamic mechanism that will optimize the blue light level based on content. BlueLight shield can reduce up to 30% blue light and protect your eyes.



LUMISENSE

Acer LumiSense

LumiSense incorporates a clever content-aware process. It analyzes projected content frame by frame and dynamically adjusts image visibility to optimum levels. Thanks to LumiSense intelligent judgment and dynamic adjustment, all dark scenes are clearly displayed with no loss of detail.

About Acer

Founded in 1976, today Acer is one of the world's top ICT companies and has a presence in over 160 countries. As Acer looks into the future, it is focused on enabling a world where hardware, software and services will infuse with one another to open up new possibilities for consumers and businesses alike. From service-oriented technologies to the Internet of Things to gaming and virtual reality, Acer's 7,000+ employees are dedicated to the research, design, marketing, sale, and support of products and solutions that break barriers between people and technology. More information is at www.acer.com.