Note: This datasheet may be out of date. Please download the latest datasheet of LQG15HS22NH02# from the official website of Murata Manufacturing

# LQG15HS22NH02#

"#" indicates a package specification code.

### Designed under Industrial Global Standard
















< List of part numbers with package codes > LQG15HS22NH02J LQG15HS22NH02D LQG15HS22NH02B




## Appearance & Shape















### References

Packaging	Specifications	Minimum Order Quantity
J	330mm Paper Tape	50000
D	180mm Paper Tape	10000
В	Bulk(Bag)	1000

Mass (typ.)	
1 piece	0.001g

1 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





# LQG15HS22NH02#

Note: This datasheet may be out of date.

Please download the latest datasheet of LQG15HS22NH02# from the official website of Murata Manufacturing

"#" indicates a package specification code.

Co., Ltd.



L size	1.0±0.05mm
W size	0.5±0.05mm
T size	0.5±0.05mm
Size code inch (mm)	0402 (1005)
Inductance	22nH±3%
Inductance Test Frequency	100MHz
Rated current (Itemp) (Based on Temperature rise)	350mA
Max. of DC resistance	0.42Ω
Q(min.)	8
Q Test Frequency	100MHz
Self resonance frequency (min.)	1900MHz
Operating Temperature Range(Self- temperature rise is not included)	-55°C to 125°C
Series	LQG15HS_02

2 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





# LQG15HS22NH02#

"#" indicates a package specification code.




The charts below may show another part number which shares its characteristics.





LQG15HS22NH02 Q



LQG15HS22NH02 |Z|

3 of 3

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering

