Note: This datasheet may be out of date. Please download the latest datasheet of 1227AS-H-4R7M# from the official website of Murata Manufacturing

References

1227AS-H-4R7M#

"#" indicates a package specification code.
















< List of part numbers with package codes > 1227AS-H-4R7M=P2



Appearance & Shape







Packaging	Specifications	Minimum Order Quantity
=P2	180Embossed Tape	2000

Mass (typ.)	
1 piece	0.0651g



Rated current (Isat) is specified when the decrease of the initial inductance value at 30%. Rated current (Itemp) is specified when temperature of the inductor is raised 40°C by DC current.

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





Note: This datasheet may be out of date. Please download the latest datasheet of 1227AS-H-4R7M# from the official website of Murata Manufacturing

1227AS-H-4R7M#

"#" indicates a package specification code.



L size	3.0±0.2mm
W size	2.8±0.2mm
T size	1.8mm
Size code inch (mm)	1211 (3028)
Inductance	4.7μH±20%
Inductance Test Frequency	0.1MHz
Rated current (Isat) (Based on Inductance change)	1100mA
Rated current (Itemp) (Based on Temperature rise)	1800mA
Max. of DC resistance	0.092Ω
Operating Temperature Range (Self-temperature rise is included)	-40°C to 85°C
Class of magnetic shield	Ferrite Core
DC Resistance Intermediate Values	0.077Ω+20%/-30%
Series	DEM2818C

2 of 3

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





1227AS-H-4R7M#

"#" indicates a package specification code.




The charts below may show another part number which shares its characteristics.





1227AS-H-4R7M Q



1227AS-H-4R7M |Z|

3 of 3

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

