

Cleaning:

- > Clean this light fitting only with a soft dry cloth
- > Do not use any chemical or abrasive cleaners.

Tube replacement:

- > Switch off the electricity at the mains.
- > Release the diffuser by gently pulling out the three clips at the top of the fitting.
- > Holding the tube in the middle, pull it off of the socket in the middle of the fitting.
- > Press the new tube gently onto the socket until it clicks if the lamp does not fit easily, try rotating it through 180° and try again.
- > Replace the diffuser and close the three clips.
- > Restore the power and switch on.

Replacement tube type:

	D0130	D151
Wattage:	28 W	16 W
Supply Voltage:	240 V	240 V
Type:	Energy saving square fluorescent lamp—4 pin.	

Eventually, you may want to replace this light fitting:

When your light fitting comes to the end of its life or you choose to update or upgrade it by replacing it, please do not dispose of it with your normal household waste, please recycle where facilities exist. When you need to dispose of this fitting, check with your retailer or local authority for suitable options. New regulations will encourage the recycling of Waste from Electrical and Electronic Equipment (European "WEEE Directive" effective August 2005).



If you experience problems:

If your light is defective or develops a fault, please return it to the place where you bought it. You can call our Helpline for advice. The Helpline will gladly give advice on any aspect of any Eterna Lighting product but may not be able to give specific instructions regarding individual installations.
If in doubt, consult a qualified electrician.

Help line:

Tel: 01933 673 144 Fax: 01933 678 083 Email: sales@eterna-lighting.co.uk
For answers to frequently asked questions (FAQs) and other information visit our web-site
www.eterna-lighting.co.uk



IMPORTANT!

Safety and Installation instructions

Round Fluorescent Ceiling Fittings

Model(s)
D130, D151

Pack contents:

Ceiling fitting	1
Energy saving square fluorescent lamp—4 pin	1
Fixing kit	1

**PLEASE READ THESE INSTRUCTIONS BEFORE
INSTALLING YOUR NEW FITTING**

PLEASE RETAIN FOR FUTURE REFERENCE

Read this first:

- > **If in any doubt, consult a qualified electrician.**
- > Switch off the mains before commencing installation and remove the appropriate circuit fuse.
- > Suitable for indoor use only.
- > This product is only suitable for use in living areas (not for areas constantly subject to moisture).
- > This product is suitable for installation on surfaces with normal flammability (indicated by the "F" in a triangle) e.g. wood, plasterboard, masonry. It is not suitable for use on highly flammable surfaces (e.g. polystyrene, textiles).
- > Before making fixing hole(s), check that there are no obstructions hidden beneath the mounting surface such as pipes or cables.
- > The chosen location of your new fitting should allow for the product to be securely mounted (e.g. to a ceiling joist) and safely connected to the mains supply (lighting circuit).
- > Do not attach to surfaces which are damp, freshly painted or otherwise electrically conductive (e.g. metallic surfaces).
- > If the location of your new fitting requires the provision of a new electrical supply, the supply must conform with the requirements of the latest edition of the IEE wiring regulations.
- > This product is designed for permanent connection to fixed wiring: this should be either a suitable lighting circuit (protected with a 5 or 6 Amp MCB or fuse) or a fused spur (with a 3 Amp fuse) via a fused connection unit. We recommend that the supply incorporates a switch for ease of operation.

- > Make connections to the electrical supply in accordance with the following code:
 - Live - Brown or Red
 - Neutral - Blue or Black
 - Earth - Green and YellowAdditional red wires may be present in your ceiling that are connected to the ring live circuit. Do not connect your fitting to these wires. If these wires are not terminated in a ceiling rose, join them together in a separate terminal block (not supplied), ensure that there are no strands of wire protruding from the terminals and wrap well with insulating tape.
- > This product must be connected to Earth.

Installation:

- 1) Pull out the three clips to release the diffuser.
- 2) Thread your supply wiring through the large hole in the back of the fitting.
- 3) Secure the fitting in place using the fixings supplied or, if these fixings are not appropriate to your installation, select suitable alternatives.
- 4) Make the electrical connections according to the colour code above.
- 5) Fit the Energy saving square fluorescent lamp—4 pin (supplied) by pressing gently onto the socket in the centre of the fitting until it clicks into place. If the tube does not fit easily, try rotating it through 180° and try again.
- 6) Replace the diffuser and push the clips back into position.
- 7) Restore the power supply and switch on.

Safety markings:

