

Data sheet | Item number: 215-212

Banana plug; for socket 4 mm Ø; 2,50 mm<sup>2</sup>; red

[www.wago.com/215-212](http://www.wago.com/215-212)



Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.



## Data

### Technical Data

Main product function	Testing accessories
Total number of potentials	1

### Electrical data

Rated current	20 A
Test voltage	42 V

### Connection data

Connection technology	CAGE CLAMP®
Strip length	9 ... 11 mm / 0.35 ... 0.43 inch
Total number of connection points	1
Solid conductor	0,08 ... 2,5 mm <sup>2</sup> / 28 ... 14 AWG
Fine-stranded conductor	0,08 ... 2,5 mm <sup>2</sup> / 28 ... 14 AWG

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG  
 Hansastr. 27  
 32423 Minden  
 Phone: +49571 887-0 | Fax: +49571 887-169  
 Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
 We are always happy to take your call at +49 (571) 887-44222.



## Geometrical Data

Width	8 mm / 0.315 inch
Height	15 mm / 0.591 inch
Depth	40 mm / 1.575 inch

## Material Data

Color	red
Weight	3.9 g

## Commercial data

Product Group	2 (Terminal Block Accessories)
Packaging type	BOX
Country of origin	DE
GTIN	4045454293482
Customs tariff number	85366990990

## Counterpart

### Downloads

#### Documentation

##### Bid Text

215-212 GAEB X81 - Datei	Feb 19, 2019	xml 3.1 kB	Download
215-212 doc - Datei	Sep 19, 2017	doc 25.1 kB	Download

## CAD/CAE-Data


### CAE data

EPLAN Data Portal 215-212	URL	Download
WSCAD Universe 215-212	URL	Download

Subject to changes. Please also observe the further product documentation!


## Handling Instructions

### Inserting a conductor



Conductor termination: Press button fully, insert stripped conductor into square entry and release.

### Testing



Testing with a banana plug

(picture shows 209-170 Test Plug Adapter).

Subject to changes. Please also observe the further product documentation!