

## Manual Unassembled Syringes

- Includes barrel, rubber stopper, and plunger rod
- Available in Luer Lok™ and tapered tip styles
- Unassembled and non-calibrated



Cat No.	UPC No.	Packed	Size	Stopper	Tip	Pack Wt.		Pack Quantity
						lb	g	
M1L	037103177032	Bagged	1CC	Rubber	Luer Slip™	0.125	3.5	20
M3LL	037103177117	Bagged	3CC	Rubber	Luer Lok™	0.500	14.2	20
M3LL100	037103177124	Bagged	3CC	Rubber	Luer Lok™	0.843	23.9	100
M5LL	037103177223	Bagged	5CC	Rubber	Luer Lok™	0.280	7.9	20
M6T	037103177612	Bagged	6CC	Rubber	Tapered	0.307	8.7	20
M10LL	037103176981	Bagged	10CC	Rubber	Luer Lok™	0.317	9.0	15
M30LL	037103177087	Bagged	30CC	Rubber	Luer Lok™	0.554	15.7	10
M30T	037103177575	Bagged	30CC	Rubber	Tapered	0.547	15.5	10
M50LL	037103177179	Bagged	50CC	Rubber	Tapered	0.459	13.0	5

## Manual Assembled Calibrated Syringes

- Includes graduated barrel, rubber stopper, plunger rod, and tip cap
- Available in Luer Lok™ and tapered tip styles (50cc only)



Cat No.	UPC No.	Packed	Size	Stopper	Tip	Pack Wt.		Pack Quantity
						lb	g	
M1LASSM	037103177049	Bagged	1CC	Rubber	Luer Slip™	0.152	4.3	20
M1BA	037103177056	Boxed	1CC	Rubber	Luer Slip™	16.000	453.3	3000
M3LLASSM	037103177131	Bagged	3CC	Rubber	Luer Lok™	0.179	5.1	20
M3LLASSM100	037103177148	Bagged	3CC	Rubber	Luer Lok™	0.759	21.5	100
M3LLBA	037103177155	Boxed	3CC	Rubber	Luer Lok™	13.700	388.1	1600
M5LLASSM	037103177230	Bagged	5CC	Rubber	Luer Lok™	0.261	7.4	20
M5LLASSM100	037103177247	Bagged	5CC	Rubber	Luer Lok™	1.192	33.8	100
M5LLBA	037103177254	Boxed	5CC	Rubber	Luer Lok™	18.360	520.1	1400
M10LLASSM	037103176998	Bagged	10CC	Rubber	Luer Lok™	0.294	8.3	15
M10LLASSM100	037103177001	Bagged	10CC	Rubber	Luer Lok™	1.860	52.7	100
M10LLBA	037103177025	Boxed	10CC	Rubber	Luer Lok™	16.650	471.7	850
M20LLASSM	037103177063	Bagged	20CC	Rubber	Luer Lok™	0.358	10.1	10
M20LLBA	037103177070	Boxed	20CC	Rubber	Luer Lok™	11.890	336.8	325
M30LLASSM	037103177094	Bagged	30CC	Rubber	Luer Lok™	0.452	12.8	10
M30LLBA	037103177100	Boxed	30CC	Rubber	Luer Lok™	11.160	316.2	225
M50LLASSM	037103178251	Bagged	50CC	Rubber	Luer Lok™	0.412	11.7	5
M50LLBA	037103177193	Boxed	50CC	Rubber	Luer Lok™	11.000	311.6	125
M50TASSM	037103177209	Bagged	50CC	Rubber	Tapered	0.419	11.9	5
M50TBA	037103177216	Boxed	50CC	Rubber	Tapered	11.140	315.6	125