

# ALUMINUM IP68 NEMA/UL TYPE 4,4X, 6, 6P, 12, 13 DIE CAST

## Ordering Information

*The AN-13xx-A series is an upgraded (IP68) replacement for the AN-13xx series. The only change is the gasket. They will be stocked by SKU as the current inventory is depleted.*

Part Number Natural Finish	Part Number Black Finish	External Length (in)	External Width (in)	External Depth (in)	Weight Lb.
AN-1300-A	AN-1300-AB	3.54	1.42	1.18	0.31
AN-1301-A	AN-1301-AB	2.52	2.28	1.38	0.31
AN-1302-A	AN-1302-AB	4.53	2.56	1.18	0.50
AN-1303-A	AN-1303-AB	4.53	2.56	2.17	0.75
AN-1304-A	AN-1304-AB	4.53	3.54	2.17	0.88
AN-1305-A	AN-1305-AB	5.83	4.25	2.95	1.50
AN-1306-A	AN-1306-AB	6.73	4.76	2.17	1.50
AN-1307-A	AN-1307-AB	8.75	5.75	2.17	3.06
AN-1308-A	AN-1308-AB	8.75	5.57	3.25	4.38
AN-1309-A	AN-1309-AB	4.75	4.75	4.00	1.88
AN-1310-A	AN-1310-AB	6.25	6.25	4.00	2.19
AN-1311-A	AN-1311-AB	1.95	1.77	1.12	0.16
AN-1312-A	AN-1312-AB	3.85	2.52	1.35	0.43
AN-1313-A	AN-1313-AB	4.90	3.14	1.59	0.78
AN-1314-A	AN-1314-AB	4.90	3.14	2.26	0.94
AN-1315-A	AN-1315-AB	5.91	2.52	1.45	0.78
AN-1316-A	AN-1316-AB	6.29	3.93	2.37	1.43
AN-1317-A	AN-1317-AB	6.29	3.93	3.19	1.71
AN-1318-A	AN-1318-AB	2.19	1.61	1.22	0.12
AN-1319-A	AN-1319-AB	3.13	2.93	2.05	0.50
AN-1320-A	AN-1320-AB	4.04	2.07	1.00	0.21
AN-1321-A	AN-1321-AB	6.89	3.15	2.36	1.02
AN-1322-A	AN-1322-AB	7.87	4.72	2.95	1.70
AN-1323-A	AN-1323-AB	10.24	6.30	3.56	3.43

*Priced, sold and packaged in quantities of one  
Contact the factory for modifications*

**BUD Aluminum NEMA**



## Benefits and Features

- Pre molded continuous Silicon gasket with outstanding performance
- Rugged #ADC-12 alloy die cast aluminum box
- Available NEMA/UL 6 (natural finish) & 6P (recommended powder coated Black for extra corrosion protection)
- UL Test results exceeded the requirements in respect to IEC60529 IP68 conditions (UL Type 6P tested under 6' of water for 24 hours)
- Type 4,4X,6,6P,12,13 as listed under UL file #E194432
- Cover attaches with stainless screws torqued at 12 in-lb.
- Easily machined and modified to your particular requirements
- Offers EMC protection

## Accessories

- Aluminum internal panels ANX-91xxx series
- IP67 Cable glands IPG series Applications
- Instrument cases
- Meter cases
- Junction boxes
- Marine applications
- High Oil exposure applications
- Wet and dirty industrial applications
- Wash-down environments

**BUD Aluminum NEMA**

## Related Products

- Switches
- Pushbuttons
- Connectors
- Cable Glands

## Key Customer Contacts


- Design Engineers and Designers
- Manufacturing Engineers
- Electronic Engineers and Designers

## Questions to Ask

- Is your application exposed to occasional submersion
- Who specifies your enclosures?
- Do you need the durability of a die cast aluminum enclosure?
- Does your product require EMC protection?
- Does your product require protection from a wet or dirty environment?

## Availability

*In Stock*



Bud Industries, Inc.