

Terminal Block Double Row Barrier

multicomp PRO

**RoHS
Compliant**




Specifications:

Pitch	: 9.5mm
Terminal	: Brass, Tin plated, 0.8t
Insulator Body	: PC, Black
Screw	: #6-32, Steel, Ni plated
Operation Temperatures	: -40°C to +120°C
Rated Current	: 20Amp 300V
Insulation Withstands Volt	: 2,000V 1 min
Insulation Resistance	: 2,000MΩ at 500V DC
Wire Range	: 12AWG to 22AWG
Screw Torque	: 12 lb-in

Part Number Table

Description	Part Number
Terminal Block, Barrier 12-22AWG	MC24309
	MC24310
	MC24311
	MC24312
	MC24313
	MC24314
	MC24315
	MC24316
	MC24317
	MC24318
	MC24319
	MC24320
	MC24321
	MC24322
	MC24323
	MC24324
MC24325	
MC24326	

Diagram



Dimensions : Millimetres (Inches)

Poles	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
A(mm)	36.2	45.7	55.2	64.7	74.2	83.7	93.2	102.7	112.2	121.7	131.2	140.7	150.2	159.7	169.2
B(mm)	28.7	38.2	47.7	57.2	66.7	76.2	85.7	95.2	104.7	114.2	123.7	133.2	142.7	152.2	161.7
Poles	17	18	19	20	21	22	23	24	25	26	27	28	29	30	
A(mm)	178.7	188.2	197.7	207.2	216.7	226.2	235.7	245.2	254.7	264.2	273.7	283.2	292.7	302.2	
B(mm)	171.2	180.7	190.2	199.7	209.2	218.7	228.2	237.7	247.2	256.7	266.2	275.7	285.2	294.7	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO