

USB C Multiport Video Adapter - USB-C to 4K 60Hz DisplayPort 1.2 or 1080p VGA Monitor Adapter - USB Type-C 2-in-1 DP (HBR2 HDR)/VGA Display Converter- Thunderbolt 3 Compatible

Product ID: CDP2DPVGA



This USB-C multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a DisplayPort or VGA display. The adapter supports High Dynamic Range (HDR) and provides sharper images with enhanced video.

Two-in-One Video Connectivity with Travel in Mind

Avoid the hassle of carrying different adapters, with a 2-in-1 USB-C monitor adapter. Featuring both DisplayPort and VGA outputs, you can conveniently connect your laptop to any DP or VGA-equipped display, using this multiport adapter.

The adapter features a durable aluminum enclosure and can withstand being carried in your travel bag.

Astonishing 4K Picture Quality and HDR

The DisplayPort output on this USB-C video adapter lets you harness the audio and video capabilities that are built into your computer's USB-C connection, delivering the astonishing quality of UHD to your 4K 60Hz display. Plus, the VGA output supports HD resolutions up to 1920 x 1080, ensuring you won't have to sacrifice picture quality when connected to a VGA monitor or projector.

With HDR support, you can enjoy lifelike images with increased contrast, brightness and colors and greater luminosity than standard digital imaging.

Stylish Connectivity for Your MacBook, MacBook Pro, or Any Laptop

The USB-C display adapter has a Space Gray housing and built-in USB-C cable designed to match your Space Gray MacBook or MacBook Pro. The adapter is compatible with USB-C DP Alt Mode devices.

CDP2DPVGA is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Note: This adapter only supports a single display - you are not able to output DisplayPort and VGA video simultaneously.

Certifications, Reports and Compatibility



Applications

- Connect to virtually any DisplayPort or VGA display while traveling or in the office
- Output video to a secondary DP or VGA monitor
- Stream, view and edit 4K and HD video on your DisplayPort or VGA display

Features

- HIGH PERFORMANCE: USB C (DP Alt Mode) to DisplayPort 1.2 4K 60Hz HBR2 or VGA 1080p display adapter on a single monitor with 2ch audio, compatible with HDCP 2.2/1.4 and Thunderbolt 3 (TB3)
- FLEXIBLE VIDEO OUTPUT: 2-in-1 portable USB-C multiport video adapter converter w/ DP 1.2 or VGA, is the perfect video hub for working from a home or office workstation, boardrooms or travel
- COMPATIBILITY: USB-C adapter for devices like Dell XPS/Precision/Latitude, Lenovo ThinkPad X1 Carbon/Extreme, Surface Pro 7/Laptop 3, MacBook Pro/Air, HP Elite/EliteBook/Spectre/Zbook & Chromebook
- TESTED & VERIFIED: USB-C video adapter tested for peak performance @ 4K 60Hz (DP) & 1080p (VGA) on monitors/projectors/displays incl brands like Samsung, Dell, HP, Lenovo, Asus, Acer, LG, Sharp, Sony
- EASY TO USE: USB C (DisplayPort over USB-C) display adapter for any TB3/USB Type C laptop/tablet/smartphone & supports driverless plug & play in Windows, macOS, iPadOS, Chrome OS, Linux, Android

Hardware	Warranty	3 Years
	Audio	Yes
	AV Input	USB-C
	AV Output	DisplayPort - 1.2 VGA
	Chipset ID	Parade Technologies PS8338
Performance	Audio Specifications	DisplayPort - 2 Channel Audio VGA - No Audio Support
	Maximum Cable Distance To Display	6.6 ft [2 m]
	Supported Resolutions	DisplayPort; 3840x2160 (4K) / 60Hz VGA: 1920x1080 / 60Hz Lower resolutions and refresh rates may also be supported
	Video Revision	DisplayPort 1.2
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input
	Connector B	1 - DisplayPort Female Output 1 - VGA (15 pin, High Density D-Sub) Female Output
	Special Notes / Requirements	Note Your USB-C device must support DP Alt Mode to work with this adapter This adapter only supports a single display - you are not able to output DisplayPort and VGA video simultaneously To achieve HDR, your USB-C port must support DisplayPort 1.4 and your display must support HDMI 2.0b
Environmental	Humidity	5~90% RH (no condensation)
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-10°C to 55°C (14°F to 131°F)
Physical Characteristics	Color	Space Gray
	Material	Aluminum
	Product Height	15.000
	Product Length	2.4 in [6.2 cm]
	Product Width	44.000
	Weight of Product	50.000

Packaging Information	Package Height	20.000
	Package Length	178.000
	Package Width	80.000
	Shipping (Package) Weight	72.000
What's in the Box	Included in Package	1 - USB-C to DisplayPort and VGA Adapter

Product appearance and specifications are subject to change without notice.