

June, 2011

# 3M™ Value Duct Tape 1900

## Product Description

3M™ Value Duct Tape 1900 is a conformable cloth duct tape made with polyethylene film over cloth scrim and rubber adhesive. A good choice for non-critical applications.

## Product Features

- Polyethylene backing provides moisture resistance to tape applications.
- Rubber adhesive sticks well to many surfaces.
- Easy tear.
- Low profile.
- Individual roll wrap for easy identification.



# 3M™ Value Duct Tape 1900

## Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

## Typical Physical Properties

Property	Values		Method
Color	Silver		
Total Tape Thickness	0.147 mm	5.8 mil	ASTM D3652
Backing	Polyethylene over cloth scrim		
Adhesive	Synthetic rubber		

## Typical Performance Characteristics

Property	Values		Method	Dwell/Cure Time	Substrate	Backing	Notes
180° Peel Adhesion	6.8 N/cm	62 oz/in	ASTM D3330	72 hr	Stainless Steel	2 mil Aluminum Foil	12 in/min (305 mm/min)
Tensile Strength	33 N/cm	304 oz/in	ASTM D3759				
Elongation at Break	15 %		ASTM D3759				
Temperature Use Range	Up to 93 °C	Up to 200 °F					

# 3M™ Value Duct Tape 1900

## Available Sizes

Property	Values	
Standard Roll Length	54.9 m	60 yd
Standard Width	48, 72 mm	1.88, 2.83 in

## Handling/Application Information

### Application Ideas

- Tool box tape for non-critical uses.
- Light duty sealing and holding.
- Marking.

## Storage and Shelf Life

Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 60% R.H. in the original carton. To obtain best performance, use this product within 12 months from date of manufacture.

## Trademarks

3M is a trademark of 3M Company.

## References

Property	Values
3m.com Product Page	<a href="https://www.3m.com/3M/en_US/company-us/all-3m-products/~3M-Value-Duct-Tape-1900?N=5002385+3293241818&amp;rt=rud">https://www.3m.com/3M/en_US/company-us/all-3m-products/~3M-Value-Duct-Tape-1900?N=5002385+3293241818&amp;rt=rud</a>
Safety Data Sheet (SDS)	<a href="https://www.3m.com/3M/en_US/company-us/SDS-search/results/?gsaAction=msdsSRA&amp;msdsLocale=en_US&amp;co=ptn&amp;q=1900">https://www.3m.com/3M/en_US/company-us/SDS-search/results/?gsaAction=msdsSRA&amp;msdsLocale=en_US&amp;co=ptn&amp;q=1900</a>

## ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

# 3M™ Value Duct Tape 1900

## Information

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

# 3M™ Value Duct Tape 1900



3M United States  
3M Center  
St. Paul, MN 55144-1000  
800-362-3550  
[www.3M.com](http://www.3M.com)

Please recycle.  
© 3M 2020. All Rights Reserved.

The brands listed above are trademarks of 3M