




# 8 WSB-Quick Marking System

6

**Horizontal marking**  
Consecutive numbers each strip  
10 strips with 10 markers for each card  
for terminal block widths  
5 – 17.5 mm/0.197 – 0.689 in

**Vertical marking**  
Consecutive numbers each strip  
10 strips with 10 markers for each card  
for terminal block widths  
5 – 17.5 mm/0.197 – 0.689 in

**Vertical marking**  
Consecutive numbers each strip  
10 strips with 10 markers for each card  
for terminal block widths  
4 mm/0.157 in



Marking per card	Item-No.	Pack.-unit pcs	Marking per card	Item-No.	Pack.-unit pcs	Marking per card	Item-No.	Pack.-unit pcs
1 ... 10 (10x)	<b>209-502</b>	5 cards	1 ... 10 (10x)	<b>209-602</b>	5 cards	1 ... 10 (10x)	<b>209-702</b>	5 cards
11 ... 20 (10x)	<b>209-503</b>	5 cards	11 ... 20 (10x)	<b>209-603</b>	5 cards	11 ... 20 (10x)	<b>209-703</b>	5 cards
21 ... 30 (10x)	<b>209-504</b>	5 cards	21 ... 30 (10x)	<b>209-604</b>	5 cards	21 ... 30 (10x)	<b>209-704</b>	5 cards
31 ... 40 (10x)	<b>209-505</b>	5 cards	31 ... 40 (10x)	<b>209-605</b>	5 cards	31 ... 40 (10x)	<b>209-705</b>	5 cards
41 ... 50 (10x)	<b>209-506</b>	5 cards	41 ... 50 (10x)	<b>209-606</b>	5 cards	41 ... 50 (10x)	<b>209-706</b>	5 cards
51 ... 60 (10x)	<b>209-569</b>	5 cards	51 ... 60 (10x)	<b>249-601</b>	5 cards			
61 ... 70 (10x)	<b>209-570</b>	5 cards	61 ... 70 (10x)	<b>249-602</b>	5 cards			
71 ... 80 (10x)	<b>209-571</b>	5 cards	71 ... 80 (10x)	<b>249-603</b>	5 cards			
81 ... 90 (10x)	<b>209-572</b>	5 cards	81 ... 90 (10x)	<b>249-604</b>	5 cards			
91 ... 100 (10x)	<b>209-573</b>	5 cards	91 ... 100 (10x)	<b>249-605</b>	5 cards			
1 ... 50 (2x)	<b>209-566</b>	5 cards	1 ... 50 (2x)	<b>209-666</b>	5 cards	1 ... 50 (2x)	<b>209-766</b>	5 cards
51 ... 100 (2x)	<b>209-507</b>	5 cards	51 ... 100 (2x)	<b>209-607</b>	5 cards	51 ... 100 (2x)	<b>209-707</b>	5 cards
101 ... 150 (2x)	<b>209-508</b>	5 cards	101 ... 150 (2x)	<b>209-608</b>	5 cards	101 ... 150 (2x)	<b>209-708</b>	5 cards
151 ... 200 (2x)	<b>209-509</b>	5 cards	151 ... 200 (2x)	<b>209-609</b>	5 cards	151 ... 200 (2x)	<b>209-709</b>	5 cards
201 ... 300 (1x)	<b>209-510</b>	5 cards	201 ... 300 (1x)	<b>209-610</b>	5 cards	201 ... 300 (1x)	<b>209-710</b>	5 cards
301 ... 400 (1x)	<b>209-511</b>	5 cards	301 ... 400 (1x)	<b>209-611</b>	5 cards	301 ... 400 (1x)	<b>209-711</b>	5 cards
401 ... 500 (1x)	<b>209-512</b>	5 cards	401 ... 500 (1x)	<b>209-612</b>	5 cards	401 ... 500 (1x)	<b>209-712</b>	5 cards
501 ... 600 (1x)	<b>209-513</b>	5 cards	501 ... 600 (1x)	<b>209-613</b>	5 cards	501 ... 600 (1x)	<b>209-713</b>	5 cards
601 ... 700 (1x)	<b>209-514</b>	5 cards	601 ... 700 (1x)	<b>209-614</b>	5 cards	601 ... 700 (1x)	<b>209-714</b>	5 cards
701 ... 800 (1x)	<b>209-515</b>	5 cards	701 ... 800 (1x)	<b>209-615</b>	5 cards	701 ... 800 (1x)	<b>209-715</b>	5 cards
801 ... 900 (1x)	<b>209-516</b>	5 cards	801 ... 900 (1x)	<b>209-616</b>	5 cards	801 ... 900 (1x)	<b>209-716</b>	5 cards
901 ... 1000 (1x)	<b>209-517</b>	5 cards	901 ... 1000 (1x)	<b>209-617</b>	5 cards	901 ... 1000 (1x)	<b>209-717</b>	5 cards
1 ... 9, ; (10x)	<b>209-565</b>	5 cards	1001 ... 1100 (1x)	<b>209-688</b>	5 cards	1 ... 9, ; (10x)	<b>209-765</b>	5 cards
<b>for double deck terminal blocks</b>			1101 ... 1200 (1x)	<b>209-669</b>	5 cards			
1, 3, 5, ... 99,			1201 ... 1300 (1x)	<b>209-670</b>	5 cards			
and 2, 4, 6, ... 100 (1x)	<b>209-599</b>	5 cards	1301 ... 1400 (1x)	<b>209-671</b>	5 cards			
			1401 ... 1500 (1x)	<b>209-672</b>	5 cards			
<b>for triple deck terminal blocks</b>			1501 ... 1600 (1x)	<b>209-901</b>	5 cards			
1, 4, 7, ... 99 (1x)	<b>249-557</b>	5 cards	1601 ... 1700 (1x)	<b>209-902</b>	5 cards			
100, 103, 106, ... 198 (1x)	<b>249-558</b>	5 cards	1701 ... 1800 (1x)	<b>209-903</b>	5 cards			
			1801 ... 1900 (1x)	<b>209-912</b>	5 cards			
plain,	<b>209-501</b>	5 cards	1901 ... 2000 (1x)	<b>209-913</b>	5 cards			
for self-			1 ... 9, ; (10x)	<b>209-665</b>	5 cards			
marking			101, 101, 101, ...					
			... 130, 130, 130 (1x)	<b>209-667</b>	5 cards			
<b>Marking pen</b>	<b>210-110</b>	1	131, 131, 131, ...					
<b>with fibre tip,</b>			... 160, 160, 160 (1x)	<b>209-668</b>	5 cards			
for permanent marking			plain,					
			<b>for double deck terminal blocks</b>					
<b>WSB-Double marker carrier, 4 mm/0.157 in wide</b>	<b>209-128</b>	100	1, 3, 5, 7, 9, 11, ... 99 and 2, 4, 6, 8, 10, 12, ... 100 (1x)	<b>209-699</b>	5 cards	plain,	<b>209-701</b>	5 cards
(see also page 1.25)				<b>209-900</b>	5 cards	for self-		
				<b>for triple deck terminal blocks</b>		marking		
				1, 4, 7, ... 99 (1x)				
				<b>249-657</b>	5 cards	<b>Marking pen</b>	<b>210-110</b>	1
				100, 103, 106, ... 198 (1x)		<b>with fibre tip,</b>		
				<b>249-658</b>	5 cards	for permanent marking		
						<b>WSB-Double marker carrier, 4 mm/0.157 in wide</b>	<b>209-128</b>	100
						(see also page 1.25)		