

PRODUCT-DETAILS

AP75

AP75 Junction box IP65



General Information

Extended Product Type	AP75
Product ID	2TKA140010G1
EAN	6410016125200
Catalog Description	AP75 Junction box IP65

Long Description	The AP75 junction box (2,5 mm ² , 450 V) is equipped with fixed, two-component membranelid cable entries, 10 in the sides and three on the bottom. It has a stiff frame (75 x 75 mm). Suitable for cables up to Ø 18. The locks box by snapping and can be opened by inserting a screwdriver into the opening slots. Pull-out brackets make it possible to mount it to a conductive base. The box can also be sealed. Mounting temperature -15...+60 °C. Made of halogen free material (IEC/61249-2-21).
------------------	---

Ordering

E-Number (Sweden)	1438410
EAN	6410016125200
Minimum Order Quantity	5 piece
Customs Tariff Number	39259080

Dimensions

Product Net Width	75 mm
Product Net Height	0.038 m
Product Net Length	75 mm
Product Net Depth / Length	75 mm

Product Net Weight	0.0501 kg
--------------------	-----------

Container Information

Package Level 1 Units	5 piece
Package Level 1 Width	0.026 m
Package Level 1 Height	0.17 m
Package Level 1 Depth / Length	0.38 m
Package Level 1 Gross Weight	0.258 kg
Package Level 2 Units	50 piece
Package Level 2 Width	0.26 m
Package Level 2 Height	0.17 m
Package Level 2 Depth / Length	0.38 m
Package Level 2 Gross Weight	2.84 kg
Package Level 3 Units	2250 piece
Package Level 3 Width	1.2 m
Package Level 3 Height	1.1 m
Package Level 3 Depth / Length	0.8 m
Package Level 3 Gross Weight	127.8 kg

Additional Information

Color	White
Degree of Protection	IP65
Entrance Type	Type of housing feed-through: Seal membrane
Material	Plastic
Mounting Type	Universal
Product Main Type	Surface mounted junction boxes
Product Name	Junction box IP65
Rated Insulation Voltage (U _i)	400 V
Shape	Square
Surface Finishing	Untreated

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	9AKK10103A2549
Declaration of Conformity - CE	9AKK106713A4627
Instructions and Manuals	9AKK10103A2549
RoHS Information	9AKK106713A4634

Classifications

ETIM 5	EC002600 - Box/housing for surface mounting on the wall/ceiling
ETIM 6	EC002600 - Box/housing for surface mounting on the wall/ceiling
ETIM 7	EC002600 - Box/housing for surface mounting on the wall/ceiling
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Installation Materials → Surface Mounted Boxes → Outdoors or Applications in Wet Spaces

