



# MASTER TL-D Super 80

## MASTER TL-D Super 80 38W/830 SLV/25

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	12000 h
Life to 50% Failures (Nom)	15000 h
Life to 50% Failures Preheat (Nom)	20000 h
LSF 2000 h Rated	99 %
LSF 4000 h Rated	97 %
LSF 6000 h Rated	96 %
LSF 8000 h Rated	95 %
LSF 12000 h Rated	89 %
LSF 16000 h Rated	33 %
LSF 20000 h Rated	2 %
Light Technical	
Color Code	830 [ CCT of 3000K]
Luminous Flux (Nom)	3350 lm
Luminous Flux (Rated) (Nom)	3350 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	88 lm/W
Color Rendering Index (Nom)	>80


LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %
Operating and Electrical	
Power (Nom)	38.0 W
Lamp Current (Nom)	0.430 A
Temperature	
Design Temperature (Nom)	25 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	2.0 mg

# MASTER TL-D Super 80

Energy Consumption kWh/1000 h	45 kWh
<b>Product Data</b>	
Full product code	871150055880040
Order product name	MASTER TL-D Super 80 38W/830 SLV/25
EAN/UPC - Product	8711500558800
Order code	927923583014

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927923583014
Net Weight (Piece)	133.000 g
ILCOS Code	FD-38/30/1B-E-G13


## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 38W/830 SLV/25	28 mm	1047.0 mm	1054.1 mm	1051.7 mm	1061.2 mm

## TL-D 38W/830

## Photometric data



LDPB\_TL-D8\_830\_0001-Spectral power distribution B/W



LDPO\_TL-D8\_830\_0001-Spectral power distribution Colour

# MASTER TL-D Super 80

## Lifetime



LDLE\_TL-D8\_0001-Life expectancy diagram

LDLE\_TL-D8\_0002-Life expectancy diagram



LDLM\_TL-D8\_0001-Lumen maintenance diagram

