

AC / DC Clamp Meters

multicomp PRO



Specifications	MP760607	MP760608
AC current (A)	0.04 to 400A ±(2%+10)	0.06 to 600A ±(2%+5)
AC voltage (V)	600V ±(0.8%+5)	
AC voltage frequency (Hz)	10Hz to 10kHz ±(0.5%+2)	
DC Current (A)	0.04 to 400A ±(2%+5)	0.06 to 600A ±(2%+5)
DC voltage (V)	600V ±(0.5%+2)	
Resistance (Ω)	40MΩ ±(0.8%+2)	60MΩ ±(0.8%+2)
Capacitance (F)	40mF ±(4%+5)	60mF ±(4%+5)
Temperature (°C)	-	-40 to +1000 ±(1.5%+5)
Frequency (Hz)	10Hz to 10MHz ±(0.1%+4)	
Display count	4000	6000
Auto range	√	
Jaw opening	28mm	
True RMS	√	
NCV	√	
Continuity test	√	
Diode	√	
MAX/MIN	√	
Relative mode	√	
Zero mode	√	
Data hold	√	
Low battery indication	√	
Auto power off	√	
General Characteristics		
Power	1.5V battery (AAA) x 2	
Display	37mm x 25mm	
Product net weight	235g	248g
Product size	215mm x 63mm x 36mm	
Standard accessories	Batteries, Test Leads, English manual	Batteries, Test Leads, Thermocouple, English manual

Part Number Table

Description	Part Number
AC / DC Clamp Meter, 4000 Count, 400A	MP760607
AC / DC Clamp Meter, 6000 Count, 600A	MP760608

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO