



MASTER TL-D Super 80

MASTER TL-D Super 80 58W/830 1SL/25

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Product data


General Information			
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	LLMF 2000 h Rated	96 %
Life To 10% Failures (Nom)	12000 h	LLMF 4000 h Rated	95 %
Life to 50% Failures (Nom)	15000 h	LLMF 6000 h Rated	94 %
Life to 50% Failures Preheat (Nom)	20000 h	LLMF 8000 h Rated	93 %
LSF 2000 h Rated	99 %	LLMF 12000 h Rated	92 %
LSF 4000 h Rated	99 %	LLMF 16000 h Rated	91 %
LSF 6000 h Rated	99 %	LLMF 20000 h Rated	90 %
LSF 8000 h Rated	99 %		
LSF 12000 h Rated	89 %	Operating and Electrical	
LSF 16000 h Rated	33 %	Power (Nom)	58.5 W
LSF 20000 h Rated	2 %	Lamp Current (Nom)	0.670 A
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	Design Temperature (Nom)	25 °C
Luminous Flux (Nom)	5240 lm		
Luminous Flux (Rated) (Nom)	5240 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	Yes
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	90 lm/W	Approval and Application	
Color Rendering Index (Nom)	>80	Energy Efficiency Label (EEL)	A
		Mercury (Hg) Content (Nom)	2.0 mg

MASTER TL-D Super 80

Energy Consumption kWh/1000 h	68 kWh
Product Data	
Full product code	871150063213540
Order product name	MASTER TL-D Super 80 58W/830 1SL/25
EAN/UPC - Product	8711500632135
Order code	927922083023

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927922083023
Net Weight (Piece)	167.000 g
ILCOS Code	FD-58/30/1B-E-G13


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 58W/830 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm

TL-D 58W/830

Photometric data





LDPB_TL-D8_830_0001-Spectral power distribution B/W



LDPO_TL-D8_830_0001-Spectral power distribution Colour


MASTER TL-D Super 80

Lifetime



LDLE_TL-D8_0001-Life expectancy diagram

LDLE_TL-D8_0002-Life expectancy diagram



LDLM_TL-D8_0001-Lumen maintenance diagram

