



# CorePro LEDbulbs

## CorePro LEDbulb ND 12.5-100W A60 E27 840

CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings and minimize maintenance cost. The CorePro LED bulb is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

### Product data

General Information	
Cap-Base	E27 [ E27]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	12.5-100W
Light Technical	
Color Code	840 [ CCT of 4000K]
Beam Angle (Nom)	200 °
Luminous Flux (Nom)	1521 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	121.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	12.5 W
Lamp Current (Nom)	115 mA

Wattage Equivalent	100 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	85 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	13 kWh
Product Data	
Full product code	871869651030800
Order product name	CorePro LEDbulb ND 12.5-100W A60 E27 840

# CorePro LEDbulbs

EAN/UPC - Product	8718696510308
Order code	929001312402
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

Material Nr. (12NC)	929001312402
Net Weight (Piece)	0.076 kg



## Dimensional drawing



Product	D	C
CorePro LEDbulb ND 12.5-100W A60 E27 840	60 mm	110 mm


A60 220-240V 12.5W-100W 4000K E27 ND

## Photometric data



CorePro LEDbulb 100W E27 840 FR A60

CorePro LEDbulb 100W E27 840 FR A60




CorePro LEDbulb 100W E27 840 FR A60

# CorePro LEDbulbs

## Lifetime



LEDbulb 100W E27 840 FR A60



LEDbulb 100W E27 840 FR A60

