



# MASTER PL-L 4 Pin

## MASTER PL-L 36W/865/4P 1CT/25

MASTER PL-L is a medium to high-wattage linear compact fluorescent lamp, typically used for general-illumination ceiling luminaires in retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. It is designed for operation on electromagnetic as well as electronic HF control gear and is provided with a plug-in/pull-out lamp base.

### Product data

General Information	
Cap-Base	2G11 [ 2G11]
Life To 10% Failures (Nom)	10000 h
Life to 50% Failures (Nom)	15000 h
Life to 50% Failures Preheat (Nom)	20000 h
System Description	-
LSF 2000 h Rated	99 %
LSF 4000 h Rated	98 %
LSF 6000 h Rated	96 %
LSF 8000 h Rated	94 %
LSF 12000 h Rated	80 %
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	98 %
LSF Preheat 8000 h Rated	97 %
LSF Preheat 16000 h Rated	82 %
LSF Preheat 20000 h Rated	50 %
Light Technical	
Color Code	865 [ CCT of 6500K]

Luminous Flux (Nom)	2900 lm
Luminous Flux (Rated) (Nom)	2880 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color Rendering Index (Nom)	80
LLMF 2000 h Rated	93 %
LLMF 4000 h Rated	91 %
LLMF 6000 h Rated	90 %
LLMF 8000 h Rated	89 %
LLMF 12000 h Rated	87 %
LLMF 16000 h Rated	88 %
LLMF 20000 h Rated	87 %
Operating and Electrical	
Power (Nom)	36 W
Lamp Current (Nom)	0.435 A

# MASTER PL-L 4 Pin

## Temperature

Design Temperature (Nom)	30 °C
--------------------------	-------

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Cap-Base Information	4 Pins
----------------------	--------


## Approval and Application

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	40 kWh

## Product Data

Full product code	871150063520440
Order product name	MASTER PL-L 36W/865/4P 1CT/25
EAN/UPC - Product	8711500635204
Order code	927903486570
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927903486570
Net Weight (Piece)	104.000 g
ILCOS Code	FSD-36/65/1B-E-2G11

## Dimensional drawing




PL-L 36W/865/4P

## Product

MASTER PL-L 36W/865/4P 1CT/25

## Photometric data



LDPB\_PLL4P\_865-Spectral power distribution B/W

LDPO\_PLL4P\_865-Spectral power distribution Colour

## MASTER PL-L 4 Pin

