



MASTER PL-L 4 Pin

MASTER PL-L 40W/830/4P 1CT/25

MASTER PL-L is a medium to high-wattage linear compact fluorescent lamp, typically used for general-illumination ceiling luminaires in retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. It is designed for operation on electromagnetic as well as electronic HF control gear and is provided with a plug-in/pull-out lamp base.

Product data

General Information	
Cap-Base	2G11 [2G11]
Life to 50% Failures Preheat (Nom)	20000 h
System Description	High Frequency
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	98 %
LSF Preheat 8000 h Rated	97 %
LSF Preheat 16000 h Rated	82 %
LSF Preheat 20000 h Rated	50 %
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux (Nom)	3500 lm
Luminous Flux (Rated) (Nom)	3500 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	88 lm/W
Color Rendering Index (Nom)	>80
LLMF 2000 h Rated	95 %

LLMF 4000 h Rated	94 %
LLMF 6000 h Rated	93 %
LLMF 8000 h Rated	92 %
LLMF 12000 h Rated	91 %
LLMF 16000 h Rated	90 %
LLMF 20000 h Rated	90 %

Operating and Electrical	
Power (Nom)	40.0 W
Lamp Current (Nom)	0.320 A

Temperature	
Design Temperature (Nom)	30 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Cap-Base Information	4 Pins

MASTER PL-L 4 Pin

Approval and Application


Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	44 kWh

Product Data

Full product code	871150061094240
Order product name	MASTER PL-L 40W/830/4P 1CT/25
EAN/UPC - Product	8711500610942

Order code	927908208370
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927908208370
Net Weight (Piece)	134.000 g
ILCOS Code	FSDH-40/30/1B-L/P-2G11

Dimensional drawing




PL-L 40W/830/4P HF

Product

MASTER PL-L 40W/830/4P 1CT/25

Photometric data



LDPB_PLL4P_830-Spectral power distribution B/W

LDPO_PLL4P_830-Spectral power distribution Colour

