

## USB 3.0 SuperSpeed Device Cable (AB M/M) Black, 3 ft.

MODEL NUMBER: **U322-003-BK**



### Highlights

- 3-ft SuperSpeed USB 3.0 A-B Cable
- 10 times faster than USB 2.0 with transfer rates up to 5 Gbps

### System Requirements

- Computers and peripherals with USB 3.0 capability

### Package Includes

- 3-ft. USB 3.0 SuperSpeed A-B Device Cable - Black

Connect USB 3.0 computers to USB 3.0 enabled peripherals such as hard drives and printers.

### Description

Tripp Lite's SuperSpeed USB 3.0 cable brings significant performance enhancements to the ubiquitous USB standard while remaining compatible with the billions of USB enabled devices currently deployed in the market. SuperSpeed USB will deliver 10x the data transfer rate of Hi-Speed USB (up to 5Gbps) as well as improved power efficiency. USB 3.0 utilizes a bi-directional data interface rather than USB 2.0's half-duplex arrangement where data can only flow in one direction at a time, giving a ten-fold increase in theoretical bandwidth.

### Features

- 3-ft USB 3.0 SuperSpeed Cable - Black
- SuperSpeed USB is 10 times faster than Hi-Speed USB, with transfer rates up to 5 Gbps
- Sync-N-Go technology minimizes user wait-time
- Provides Optimized Power Efficiency...No device polling and lower active and idle power requirements
- Backwards compatible with USB 2.0. Devices operate with USB 2.0 platforms. Hosts support USB 2.0 legacy devices

## Specifications

OVERVIEW	
UPC Code	037332183118
INPUT	
Cable Length (ft.)	3



Cable Length (m)	0.9
<b>PHYSICAL</b>	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.5MM
Color	Black
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	0.64 x 5.08 x 22.35
Shipping Dimensions (hwd / in.)	0.25 x 2.00 x 8.80
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	10% to 85%, Non-Condensing
<b>CONNECTIONS</b>	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps)
Technology	USB 3.0 (SuperSpeed); USB
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>